





# 浮动接头



CAD  
2D 3D

标准加工图

①代号	类型		M材质		H硬度	S表面处理	
			国标	相当			
FNCIMA	内螺纹型	标准型	尺寸固定型	45	S45C	斜线部 43~48HRC 表面高频淬火	发黑
FNCIMB			9Cr18Mo	SUS440C	—		
FNCINA	内螺纹型	标准型	尺寸指定型	45	S45C	斜线部 43~48HRC 表面高频淬火	发黑
FNCINB			9Cr18Mo	SUS440C	—		



①代号 - ②M - ③H  
 FNCIMA - M8  
 FNCINA - M8 - H30

型号		③H		气缸连接件							
①代号	②M	固定型	指定型(最小单位1)	Mx螺距	F	A	J	L	E	h	SR
FNCIMA FNCIMB FNCINA FNCINB	3	15	—	3x0.5	6	12	17	5	10	6	40
	4			4x0.7	8						
	5			5x0.8	10						
	6	20	—	6x1.0	12	14	19	6	12	8	50
	8			8x1.25	14						
	10	25	30~60	10x1.25	15	20	27	8	17	10	60
	12			12x1.25	18						
	14			14x1.5	21						
	16	45	50~100	16x1.5	24	32	43	12	27	15	100
	18			18x1.5	27						
	20			20x1.5	30						
	22	60	60~100	22x1.5	33	40	52	15	32	18	200
	24			24x1.5	36						
	30			30x1.5	43						
	36	65	—	36x1.5	45	54	69	18	46	24	250
				48							

▲SUS440C淬火件可能因淬火而变色。

