



★ 产品特点: 开口双孔固定型上面有沉孔。

| 类型 | M材质 | S表面处理 | A附件 |
|--------|--------|----------|--------------|
| SCABAG | 一般结构用钢 | 四氧化三铁保护膜 | 1个内六角螺栓 |
| SCAEAG | | 无电解镀锌 | 1个内六角螺栓(不锈钢) |
| SCANAG | 不锈钢 | - | |

⚠ 如对防锈有要求, 请优先选用不锈钢材质或无电解镀锌产品。

其余 $\sqrt{25}$

视角标准: 第一视角



①代号 - ②D - ③B
SCABAG - D12 - B10

| ①代号 | 主要尺寸 | | | | | | | | | | | | | | | |
|----------------------------|------|----|----------------|-------|-----|----------------|------|------|-----|----|-----|----------------|----------------|----------------|-----|--|
| | ②D | ③B | D ₁ | M(粗牙) | d | d ₁ | ds | DS | S | K | a | T ₁ | T ₂ | T ₃ | C | |
| SCABAG SCAEAG SCANAG | 6 | 8 | 24 | M3 | 3.4 | 6 | 3.5 | 6.5 | 3.3 | 15 | 1 | 8 | 4 | 6-8 | 0.5 | |
| | | 10 | 24 | M4 | 4.5 | 7.5 | 3.5 | 6.5 | 3.3 | 15 | | 8 | 4 | | | |
| | 8 | 8 | 25 | M3 | 3.4 | 6 | 3.5 | 6.5 | 3.3 | 17 | 1 | 8 | 5 | 7-9 | | |
| | | 10 | 28 | M4 | 4.5 | 7.5 | 4.5 | 8 | 4.4 | 18 | | 9 | 5 | 8-9 | | |
| | 10 | 12 | 33 | M4 | 4.5 | 7.5 | 5.5 | 9.5 | 5.4 | 22 | 1 | 10 | 5 | 10-11 | | |
| | | 15 | 36 | M6 | 6.6 | 12 | 6.6 | 11 | 6.5 | 23 | | 11 | 5 | | | |
| | 12 | 10 | 35 | M4 | 4.5 | 7.5 | 5.5 | 9.5 | 5.4 | 24 | 1 | 11 | 5 | 10-12 | | |
| | | 15 | 35 | M5 | 5.5 | 9 | 5.5 | 9.5 | 5.4 | 24 | | 11 | 5 | | | |
| | 13 | 10 | 38 | M6 | 6.6 | 12 | 6.6 | 11 | 6.5 | 25 | 1 | 13 | 6 | 11-13 | | |
| | | 12 | 33 | M4 | 4.5 | 7.5 | 4.5 | 8 | 4.4 | 23 | | 11 | 5 | | | |
| | 15 | 12 | 36 | M5 | 5.5 | 9 | | | | 25 | 1.5 | 12 | 6 | 11-13 | | |
| | | 15 | 36 | M6 | 6.6 | 12 | 5.5 | 9.5 | 5.4 | 25 | | 13 | 8 | | | |
| | 16 | 12 | 40 | M6 | 6.6 | 12 | 6.6 | 11 | 6.5 | 28 | 1 | 13 | 8 | 11-12 | | |
| | | 15 | 36 | M5 | 5.5 | 9 | 4.5 | 8 | 4.4 | 26 | | 12 | 6 | | | |
| | 20 | 12 | 38 | M5 | 5.5 | 9 | 5.5 | 9.5 | 5.4 | 28 | 1 | 13 | 6 | 12-13 | | |
| | | 15 | 42 | M6 | 6.6 | 12 | 6.6 | 11 | 6.5 | 29 | | 13 | 8 | | | |
| | 25 | 12 | 42 | M5 | 5.5 | 9 | 5.5 | 9.5 | 5.4 | 32 | 1 | 15 | 7 | 13-14 | | |
| | | 15 | 42 | M5 | 5.5 | 9 | 5.5 | 9.5 | 5.4 | 32 | | 15 | 7 | | | |
| | 30 | 12 | 45 | M6 | 6.6 | 12 | 6.6 | 11 | 6.5 | 33 | 1 | 15 | 8 | 14-15 | | |
| | | 15 | 45 | M6 | 6.6 | 12 | 6.6 | 11 | 6.5 | 33 | | 16 | 8 | | | |
| | 35 | 12 | 48 | M5 | 5.5 | 9 | 5.5 | 9.5 | 5.4 | 37 | 1 | 17 | 7 | 14-16 | | |
| | | 15 | 50 | | | | | | | 38 | | 18 | 10 | | | |
| | 40 | 15 | 55 | M6 | 6.6 | 12 | 6.6 | 11 | 6.5 | 43 | 1 | 20 | 10 | 15-17 | | |
| | | 18 | 60 | | | | | | | 48 | | 20 | 10 | | | |
| 50 | 18 | 78 | M8 | 9 | 14 | 9 | 14 | 8.6 | 60 | 2 | 23 | 12 | 21 | | | |
| | 22 | 88 | M10 | 11 | 18 | 11 | 17.5 | 10.8 | 71 | | 28 | 13 | | | | |



交货期 **5天发货**



| 数量分类 | 标准订单 | 特殊订单 |
|------|------|---------|
| | 数量 | 小单 1-50 |
| 交货期 | 5天发货 | 另行报价 |

⚠ 常州东莞发货遇特殊期间交期有变更。
⚠ 部分型号为5天发货, 请以报价为准。

库存品

