



视角标准：第一视角



① 型号

BSAC0806-S

① 型号	行程(mm)	每次最大吸收能量(kgf.m)	有效重量(kg)	冲击速度(m/s)	每小时吸收能量(Nm)	使用温度(°C)	重量(g)
BSAC0604(N)	4	0.5	3	1	720	-10~+80	4
BSAC0806-S(N)	6	3	0.9~6	2.5	7000	-10~+80	17
BSAC1007-S(N)	7	6	1.3~12	2.5	12400	-10~+80	28
BSAC1412-S(N)	12	20	12~40	1.6	33000	-10~+80	70
BSAC1412-SM(N)	12	20	14~50	2.5	30000	-10~+80	60
BSAC2015-S(N)	15	59	40~120	4.0	38000	-10~+80	160

① 型号	螺纹公称	行程 (mm)	A	B	C	D	E	F	G	H	I
BSAC0604(N)	M6×0.75	4	32.7	27.7		1.8		22.7	1	8	3
BSAC0806-S(N)	M8×1.0	6	55.6	40.1	6.8	2.9	8.5	35.1	1	11	4
BSAC1007-S(N)	M10×1.0	7	62.8	45.5	8.8	2.9	8.8	40	1.5	12.7	4
BSAC1412-S(N)	M14×1.5	12	90	65.5	12	5	11	60.5	1.5	19	5
BSAC1412-SM(N)	M14×1.5	13	78	53.5	12	3.8	11	48.5	1.5	19	5
BSAC2015-S(N)	M20×1.5	15	104	71	17.8	6	16	64	2	26	8

▲ 无需撞击头型号-N。列BSAC1007-S-N