



①代号 - ②尺寸系列
NGDLF - 0402A

①代号	②尺寸系列	D	T	L ₁	L ₂	S ₁	S ₂	H	D×d(φ)
NGDLF	0405B		M5	17	18	8	10	5	
	0401A		R1/8	19	18	8	12	8	
	0402A	φ4	R1/4	21	18	8	17	10	4×φ2.5
	0403A		R3/8	22	18	8	19	10.5	
	0404A		R1/2	24	18	8	24	12	
	0605B		M5	17	19	10	10	5	
	0601A		R1/8	19	19	10	12	8	
	0602A	φ6	R1/4	21	19	10	17	10	6×φ4
	0603A		R3/8	22	19	10	19	10.5	
	0604A		R1/2	24	19	10	24	12	
	0801A		R1/8	20	23	14	14	8	
	0802A		R1/4	22	23	14	17	10	
	0803A	φ8	R3/8	23	23	14	19	10.5	8×φ5
	0804A		R1/2	25	23	14	24	12	
	1001A		R1/8	21.5	25	15	17	8	
	1002A		R1/4	23.5	25	15	17	10	
	1003A	φ10	R3/8	24.5	25	15	19	10.5	10×φ6.5
	1004A		R1/2	26.5	25	15	24	12	
	1201A		R1/8	24	28	17	17	8	
	1202A		R1/4	26	28	17	17	10	
1203A	φ12	R3/8	27	28	17	19	10.5	12×φ8	
1204A		R1/2	29	28	17	24	12		
1403A		R3/8	30	31.5	19	19	10.5		
1404A	φ14	R1/2	32	31.5	19	24	12	14×φ10	
1603A		R3/8	30	33.5	21	21	10.5		
1604A	φ16	R1/2	32	33.5	21	24	12	16×φ12	
1606A		R3/4	34	33.5	21	32	15		

L1
气动接头