









按图定制

①代号	边长	④材质	⑤表面处理	最高使用压力
MALBGT	25×25	铝合金	-	1MPa(≈10.2Kgf/cm²)以下
MALBGU	35×35			

MALBGT (边长25×25)  
MALBGU (边长35×35)



视角标准：第一视角



①代号 - ②侧面孔数K - ③螺纹代号L

MALBGT - K2 - L55

MALBGT  
(25×25)

MALBGU  
(35×35)

①代号	②侧面孔数K	③螺纹代号L	d Rc(PT)/M
	K	L	
MALBGT (25×25)	1	11 55	1/8 M5
	2	11 55	1/8 M5
	3	11 55	1/8 M5
	4	11 55	1/8 M5
	5	11 55	1/8 M5
	6	11 55	1/8 M5
MALBGU (35×35)	1	22N	1/4
	2		
	3		
	4		
	5		
	6		

▲ 螺纹代号：如11，表示d为1/8管螺纹。



爱安特自营商城焕新登场，线上下单，疾速送达



400-6699-428



www.ant-fa.com

L5  
歧管块