




★ 产品特点：与高品质相比，性价比更高。




CAD 2D/3D

RoHS


标准加工袋

型式	齿面保护层	材 质	芯 线
ABRN-H8M	尼龙帆布	氯丁橡胶	玻璃纤维

⚠ 使用温度-20~80°C。



ABRN-H8M H8M型



视角标准：第一视角




① 代号 - ② 齿形 ③ 公称宽度 - ④ 编号

ABRN - H8M060 - 160

订购编号示例

ABRN-H8M (齿距: 8mm)					
① 代号	② 齿形	③ 公称宽度	④ 编号	周长(mm)	齿数
ABRN	H8M	150 (15mm)	112	112	14
			184	184	23
			288	288	36
			304	304	38
			320	320	40
			328	328	41
			336	336	42
			344	344	43
			352	352	44
			360	360	45
			368	368	46
			376	376	47
			384	384	48
			392	392	49
			400	400	50
		408	408	51	
		416	416	52	
		424	424	53	
		432	432	54	
		440	440	55	
		448	448	56	
		456	456	57	
		464	464	58	
		472	472	59	
		480	480	60	
		488	488	61	
		496	496	62	
		504	504	63	
		512	512	64	
		520	520	65	
		528	528	66	
		536	536	67	
		544	544	68	
		552	552	69	
		560	560	70	
		568	568	71	
		576	576	72	
		584	584	73	
		592	592	74	
		600	600	75	
608	608	76			
616	616	77			
624	624	78			
632	632	79			
640	640	80			
648	648	81			
656	656	82			
664	664	83			
672	672	84			
680	680	85			
688	688	86			
696	696	87			
704	704	88			
712	712	89			
720	720	90			
728	728	91			
736	736	92			
744	744	93			
752	752	94			
760	760	95			
768	768	96			
776	776	97			
784	784	98			
792	792	99			
800	800	100			

ABRN-H8M (齿距: 8mm)					
① 代号	② 齿形	③ 公称宽度	④ 编号	周长(mm)	齿数
ABRN	H8M	150 (15mm)	808	808	101
			816	816	102
			824	824	103
			832	832	104
			840	840	105
			848	848	106
			856	856	107
			864	864	108
			872	872	109
			880	880	110
			888	888	111
			896	896	112
			904	904	113
			912	912	114
			920	920	115
		928	928	116	
		936	936	117	
		944	944	118	
		952	952	119	
		960	960	120	
		968	968	121	
		976	976	122	
		984	984	123	
		992	992	124	
		1000	1000	125	
		1008	1008	126	
		1016	1016	127	
		1024	1024	128	
		1032	1032	129	
		1040	1040	130	
		1048	1048	131	
		1056	1056	132	
		1064	1064	133	
		1072	1072	134	
		1080	1080	135	
		1088	1088	136	
		1096	1096	137	
		1104	1104	138	
		1112	1112	139	
		1120	1120	140	
1128	1128	141			
1136	1136	142			
1144	1144	143			
1152	1152	144			
1160	1160	145			
1168	1168	146			
1176	1176	147			
1184	1184	148			
1192	1192	149			
1200	1200	150			
1208	1208	151			
1216	1216	152			
1224	1224	153			
1232	1232	154			
1240	1240	155			
1248	1248	156			
1256	1256	157			
1264	1264	158			
1272	1272	159			
1280	1280	160			
1288	1288	161			
1296	1296	162			
1304	1304	163			
1312	1312	164			
1320	1320	165			

D4 同步带