




标准型

# 碟型弹簧



①代号	类型	圆材质
DSBA	标准型	50CrVA



视角标准：第一视角

J2  
弹簧



①代号 - ②L 载荷类型 - ③D  
DSBA - A - D8

①代号	②D	③载荷类型	d	t	H	h	h/t	25%压缩量时		50%压缩量时		75%压缩量时		重量/每1000片 (kg)
								s (mm)	F (N)	s (mm)	F (N)	s (mm)	F (N)	
DSBA	8	A	4.2	0.3	0.55	0.25	0.83	0.063	52	0.125	89	0.188	118	0.08
		B		0.4	0.6	0.2	0.5	0.05	78	0.1	147	0.15	210	0.107
	10	A	5.2	0.4	0.7	0.3	0.75	0.075	88	0.15	155	0.225	209	0.17
		B		0.5	0.75	0.25	0.5	0.063	122	0.125	228	0.188	325	0.214
	12.5	A	6.2	0.5	0.85	0.35	0.7	0.088	120	0.175	215	0.263	294	0.346
		B		0.7	1	0.3	0.43	0.075	240	0.15	457	0.225	660	0.488
	14	A	7.2	0.5	0.9	0.4	0.8	0.1	120	0.2	210	0.3	279	0.425
		B		0.8	1.1	0.3	0.38	0.075	284	0.15	547	0.225	797	0.676
	16	A	8.2	0.6	1.05	0.45	0.75	0.113	172	0.225	304	0.338	410	0.672
		B		0.9	1.25	0.35	0.39	0.088	363	0.175	697	0.263	1013	1.002
	18	A	9.2	0.7	1.2	0.5	0.71	0.125	233	0.25	417	0.375	566	0.999
		B		1	1.4	0.4	0.4	0.1	451	0.2	865	0.3	1254	1.418
	20	A	10.2	0.8	1.35	0.55	0.69	0.138	304	0.275	547	0.413	748	7.394
		B		1.1	1.55	0.45	0.41	0.113	548	0.225	1050	0.338	1521	1.913
	22.5	A	11.2	0.8	1.45	0.65	0.81	0.163	306	0.325	533	0.488	708	1.799
		B		1.25	1.75	0.5	0.4	0.125	693	0.25	1330	0.375	1929	2.814
	25	A	12.2	0.9	1.6	0.7	0.78	0.175	367	0.35	644	0.525	862	2.543
		B		1.5	2.05	0.55	0.37	0.138	1040	0.275	2007	0.413	2926	4.219
	28	A	14.2	1	1.8	0.8	0.8	0.2	476	0.4	832	0.6	1107	3.468
		B		1.5	2.15	0.65	0.43	0.163	1033	0.325	1970	0.488	2841	5.166
	31.5	A	16.3	1.25	2.15	0.9	0.72	0.225	791	0.45	1409	0.675	1913	5.384
		B		1.75	2.45	0.7	0.4	0.175	1391	0.35	2669	0.525	3871	7.546
	35.5	A	18.3	1.25	2.25	1	0.8	0.25	731	0.5	1277	0.75	1699	6.865
		B		2	2.8	0.8	0.4	0.2	1864	0.4	3576	0.6	5187	10.97
40	A	20.4	1.5	2.65	1.15	0.77	0.288	1109	0.575	1953	0.863	2621	10.53	
	B		2.25	3.15	0.9	0.4	0.225	2336	0.45	4481	0.675	6500	15.72	
45	A	22.4	1.75	3.05	1.3	0.74	0.325	1524	0.65	2701	0.975	3646	15.89	
	B		2.5	3.5	1	0.4	0.25	2773	0.5	5320	0.75	7716	22.77	
50	A	25.4	2	3.4	1.4	0.7	0.35	1949	0.7	3491	1.05	4762	22.09	
	B		3	4.1	1.1	0.37	0.275	4255	0.55	8214	0.825	11976	32.85	

▲ 标准产品执行二级以上公差精度，若需求一级精度另需注明!



新商城带来全新体验, 3D/2D图纸在线浏览与选型



400-6699-428



www.ant-fa.com