

灰铸铁直柱型/肩型/法兰型



★ 产品特点: 可用于中载、低速运行。

| ①代号 | 类型 | M材质 | | 内径公差 | 外径公差 |
|-------|-----|---------------|--------------|------|------|
| | | 国标 | 相当 | | |
| OFCBZ | 直柱型 | HT250含特殊固体润滑剂 | FC250特殊固体润滑剂 | G6 | m6 |
| OFCFZ | 肩型 | | | | h7 |
| OFCSZ | 法兰型 | | | | |

▲ 与本产品相配固定座内径公差: ± 0.02 。
 ▲ 轴径公差: e7或h9仅供参考。
 ▲ 建议使用乐泰胶粘接固定衬套。



①代号 - ②d - ③L
 OFCFZ - d12 - L15
 OFCSZ - d12

B2 无油衬套

| 型号 | | Dm6 | | ③L | | | | H | C | |
|--------------|------|------------------|----|------------------|-----|----|----|----|----|-----|
| ①代号 | ②dG6 | | | | | | | | | |
| OFCBZ 直柱型 | 6 | +0.012 +0.004 | 10 | +0.015 +0.006 | (6) | 8 | 10 | 12 | 12 | 0.3 |
| | 8 | +0.014 | 12 | +0.018 | | 8 | 10 | 12 | 15 | |
| | 10 | +0.005 | 16 | +0.007 | | 10 | 12 | 15 | 20 | |
| | 12 | | 18 | | | 10 | 12 | 15 | 20 | |
| OFCFZ 肩型 | 15 | +0.017 | 22 | +0.021 | | 15 | 20 | 25 | 30 | 24 |
| | 16 | +0.006 | 23 | +0.008 | | 15 | 20 | 25 | 30 | 25 |
| | 20 | | 28 | | | 20 | 25 | 30 | 40 | 30 |
| | 25 | +0.020 | 32 | +0.025 | | 25 | 30 | 40 | 50 | 34 |
| | 30 | +0.007 | 38 | +0.009 | | 30 | 40 | 50 | 60 | 40 |
| | | | | | | | | | | |

| 型号 | | Dh7 | | L | H | T | d ₁ | d ₂ | h | P.C.D | |
|--------------|--------|--------|----|-------------|----|----|----------------|----------------|-----|-------|----|
| ①代号 | ②dG6 | | | | | | | | | | |
| OFCSZ 法兰型 | 8 | +0.014 | 15 | 0 -0.018 | 20 | 32 | 5 | 3.5 | 6 | 3.1 | 24 |
| | 10 | +0.005 | 19 | | 25 | 40 | | | | | 29 |
| | 12 | +0.017 | 21 | 0 -0.021 | 30 | 42 | 6 | 4.5 | 7.5 | 4.1 | 32 |
| | 15 | +0.006 | 28 | | 40 | 48 | | | | | 38 |
| | 20 | | 32 | | 50 | 54 | | | | | 43 |
| | 25 | +0.020 | 40 | 0 -0.025 | 60 | 62 | 8 | 5.5 | 9 | 5.1 | 51 |
| 30 | +0.007 | 45 | | 70 | 74 | 10 | 6.6 | 11 | 6.1 | 60 | |

▲ L带()尺寸仅适用OFCBZ。



交货期

5天发货



| | | |
|-----|------|-----|
| 数量 | 1-9 | 10~ |
| 折扣率 | 100% | 现询 |