






① 代号 OFSCP	④ 材质 高强度黄铜(CAC304)镶嵌MoSe
---------------	-----------------------------

OFSCP



① 代号 - ② W - ③ T - ④ L  
OFSCP - W12.5 - T10 - L40

① 代号	② W	③ T选择	④ L			螺栓孔数	A	B	C
OFSCP	12.5	10	40			2	-	-	-
			60			3	7.5	-	-
			80			4	-	30	50
	15	10 15	60			2	7.5	-	-
			(70) 80 100			3		-	-
			80			2		-	-
	20	15 20	100 120 140			3	10	-	-
			100 120 140			3	10	-	-

▲ 带“0”的L70尺寸仅适用于T为15时的规格。

螺栓孔规格表

W	T	d1	d2	t1	W1
12.5	10	8	4.5	5	5
15	10	9.5	5.5	6	6
	15				
20	15	11	6.5	7	9
	20				
25	20	14	9	9	10



交货期

7天发货



数量

1~9

10~

折扣率

100%

现询

B2  
无油衬套

