




<b>1</b> 代号	<b>M</b> 材质	s(导槽高度)	u(导槽宽度)
OFSLCPT	高强度黄铜(CAC304)镶嵌MoS2	8	4.5

OFSLCPT



视角标准：第一视角



**1**代号 - **2**W - **3**T - **4**L  
OFSLCPT - W12.5 - T15 - L40

<b>1</b> 代号	<b>2</b> W	<b>3</b> T选择	<b>4</b> L			螺栓孔数	A
OFSLCPT	12.5	15	40			2	7.5
			50	60	70	3	
	15	15	60			2	7.5
			70	80	100	3	
20	20	80			2	10	
		100	120	140	3		

螺栓孔规格表

W	T	d <sub>1</sub>	d <sub>2</sub>	t <sub>1</sub>	w <sub>1</sub>
12.5	15	8	4.5	5	5
15	15	9.5	5.5	6	6
	20				
	25				
20	20	11	6.5	7	9
	25	14	9	9	
	30				



交货期

**7**天发货



数量

1~9

10~

折扣率

100%

现购

