

★ 产品特点: 有公制和英制螺纹可选, 材质选择多样化

①代号	类型	④材质			⑤表面处理
		本体	球状部	弹簧部	
GNAB	不锈钢油嘴	SUS303	SUS304	SUS304	光身
GNAL	黄铜镀锌油嘴	C3604	SWCH10R	SWP-B	镀锌
GNBL					
GNCL					

①代号 - ②规格
GNAB - 1

订购编号示例

型号		M	B(HEX·六角对边)	H	L	N
①代号	②规格					
GNAL	1	R1/8	10	16	7	
	2	R1/4	13	21	10	
	6	M6×0.75				
	6A	M6×1.0	8	13.5	6	
GNAB	1	R1/8	10	17.5	7.5	
	2	R1/4	14	22	11	
	6	M6×0.75				
	6A	M6×1.0	7	14	5	
GNBL	1	R1/8	10	19	7.5	12.5
	2	R1/4	14	22.5	8.8	14.2
	6	M6×0.75				
	6A	M6×1.0	8	16	6.5	10
GNCL	1	R1/8	10	19	7.5	12.5
	2	R1/4	14	22.5	8.8	14.2
	6	M6×0.75				
	6A	M6×1.0	8	16	6.5	10.2

K1
平键
圆柱销
油嘴
开口销

[分类目录](#)
[返回主目录](#)