



★ 产品特点: 符合GB894.1-1986

①代号	④材质	⑤硬度	⑥表面处理
RRCJA	弹簧钢	44-53HRC	四氧化三铁保护膜
RRCBA	304	36-44HRC	-

▲ d2是将挡圈嵌入卡簧槽内最大直径。()中的尺寸不适用材质304。
 ▲ 符合GB893.1-1986

视角标准: 第一视角

①代号 - ②公称代号
RRCJA - 5

订购编号示例

①代号	②公称代号	挡圈						参考		适用孔(参考)				min(b)	
		d ₁		t		(m)	(n)	min d ₀	d ₂	d ₃	d ₄		c		
		尺寸	公差	尺寸	公差						尺寸	公差	尺寸		公差
	(3)	2.7		0.4	+0.03 -0.06	0.8	0.95		7.2	3	2.8	0 -0.04	0.5		
	(4)	3.7	+0.04 -0.15			0.88	1.1	1	8.8	4	3.8	0			0.3
	(5)	4.7				1.12	1.25		10.7	5	4.8	-0.048	0.7		
	(7)	6.5	+0.06 -0.18	0.6	+0.04 -0.07	1.32	1.55	1.2	13.8	7	6.7	0 -0.058			0.5
	10	9.3				1.44		1.5	17.6	10	9.6				0.6
	(11)	10.2				1.52			18.6	11	10.5				0.8
	12	11				1.72			19.6	12	11.5				
	13	11.9						1.7	20.8	13	12.4				0.9
	14	12.9				1.88			22	14	13.4				
	15	13.8	+0.10 -0.36			2.00			23.2	15	14.3	0	1.1		1.1
	16	14.7		1		2.32			24.4	16	15.2	-0.11			1.2
	17	15.7							25.6	17	16.2				
	18	16.5			+0.05 -0.13	2.48			27	18	17				
	19	17.5							28	19	18				
	20	18.5							29	20	19				1.5
	(21)	19.5	+0.13 -0.42			2.68			31	21	20	0 -0.13			
	22	20.5							32	22	21				
	24	22.2				3.32		2	34	24	22.9				1.7
	25	23.2							35	25	23.9				
	28	25.9	+0.21 -0.42	1.2		3.60			38.4	28	26.6	0 -0.21	1.3		
	(29)	26.9				3.72			39.8	29	27.6			+0.14 0	2.1
	30	27.9				3.92			42	30	28.6				
	32	29.6							44	32	30.3				2.6
	(34)	31.5				4.32			46	34	32.3				
	35	32.2							48	35	33				
	36	33.2	+0.25 -0.50			4.52		2.5	49	36	34				3
	37	34.2		1.5	+0.06 -0.15				50	37	35	0 -0.25	1.7		
	38	35.2							51	38	36				
	40	36.5				5.0			53	40	37.5				3.8
	45	41.5							56	45	42.5				
	48	44.5	+0.39 -0.90						62.8	48	45.5				
	50	45.8							64.8	50	47				
	(52)	47.8				5.48			67	52	49				
	(55)	50.8		2	+0.06 -0.18				70.4	55	52		2.2		4.5
	(58)	53.8				6.12			73.6	58	55				
	60	55.8							75.8	60	57				
	(75)	70.5	+0.46 -1.10			6.32		3	92.8	75	72	0 -0.30			
	(78)	73.5							96.2	78	75				
	(80)	74.5							98.2	80	76.5				
	(82)	76.5				7			101	82	78.5		2.7		
	(85)	79.5		2.5	+0.07 -0.22				104	85	81.5				5.3
	(90)	84.5				7.6			110	90	86.5	0 -0.35			
	(95)	89.5				9.2			115	95	91.5				
	(100)	94.5	+0.54 -1.30						121	100	96.5				
	(105)	98		3		10.7		4	132	105	101	0 -0.54	3.2	+0.18 0	6

▲ ()尺寸只适用弹簧钢材质。

K1
圆柱挡圈/开口销