



★ 产品特点: 符合 JIS B 2804-2001

①代号	④材质	⑤硬度	⑥表面处理
RRCJB	弹簧钢	44-53HRC	四氧化三铁保护膜
RRCBB	SUS304	36-46HRC	-

▲ 符合GB894-2007

视角标准: 第一视角



①代号 - ②公称代号  
RRCJB - 5

①代号	②公称代号	d <sub>1</sub>		t		扣环			参考		适用轴(参考)				min(b)
		尺寸	公差	尺寸	公差	(m)	(n)	mind <sub>0</sub>	(d <sub>2</sub> )	d <sub>3</sub>	d <sub>4</sub>		c		
	3	2.7		0.25	±0.025	0.5	1.7	0.7	7	3	2.85	0.35			
	4	3.7	+0.04 -0.15	0.4	±0.03	0.9	2.2	0.8	9	4	3.8	0	0.5		0.3
	5	4.7		0.6		1.1	2.4		10.5	5	4.8	-0.04	0.7	+0.10 0	0.5
	6	5.6		0.7		1.3	2.8		12	6	5.7		0.8		0.5
	7	6.5	+0.06 -0.2	0.8	±0.04	1.4	3	1	14	7	6.7	0			0.6
	8	7.4		0.8		1.6	3		15	8	7.6	-0.06	0.9		
	10	9.3	±0.15			1.8	3	1.2	17	10	9.6	0 -0.09			
	11	10.2				2	3.1		18	11	10.5				
	12	11.1				2.1	3.2	1.5	19	12	11.5				
	13	12		1	±0.05	2.1	3.3		20	13	12.4		1.15		
	14	12.9					3.4		22	14	13.4				
	15	13.8	±0.18				3.5		23	15	14.3	0 -0.1			
	16	14.7				2.2	3.6	1.7	24	16	15.2				
	17	15.7					3.7		25	17	16.2				
	18	16.5				2.6	3.8		26	18	17				
	19	17.5					3.8		27	19	18				
RRCJB RRCBB	20	18.5					3.9		28	20	19				1.5
	21	19.5				2.7	4		30	21	20				
	22	20.5		1.2			4.1		31	22	21		1.35		
	23	21.4				2.9	4.5		32.5	23	22			+0.14 0	
	24	22.2	±0.2		±0.06		4.2	2	33	24	22.9	0 -0.2			
	25	23.2				3.1	4.3		34	25	23.9				
	26	24.2					4.4		35	26	24.9				
	28	25.9					4.6		38	28	26.6				
	29	26.9					4.7		39	29	27.6				
	30	27.9		1.5		3.5	4.8		40	30	28.6		1.65		
	32	29.6					5		43	32	30.3				
	35	32.2	±0.25			4	5.4		46	35	33				
	40	37		1.75			4.5	5.8	53	40	38	0 -0.25	1.9		
	45	41.5					4.8	6.3	58	45	42.5				
	50	45.8	±0.4		±0.07		6.7	2.5	64	50	47				2
	52	47.8		2		5	6.8		66	52	49		2.2		
	60	55.8					5.5	7.2	75	60	57	0			
	80	74.5	±0.45	2.5	±0.08	7.4	8.2		97	80	76.5	-0.3	2.7		2.5

K1  
圆柱挡圈/开口销

