


★ 产品特点: 具备良好的抗剪切力, 弹性良好。



■ 弹性销




①代号	■材质	■硬度
TXAJ	弹簧钢	45 ~ 50HRC
TXBH	不锈钢弹簧钢	42 ~ 48HRC



TXAJ



TXBH



视角标准: 第一视角



①代号 - ②D - ③L
TXAJ - D2 - L12

①代号	②D	③L	E	T	D	
			负载最小值	参考值	min	max
TXAJ TXBH	2	5 6 8 10 12 14 16 18 20	2.76	0.4	2.15	2.25
	3	6 8 10 12 14 16 18 20 22 25 28 32	6.2	0.6	3.15	3.25
	4	8 10 12 14 16 18 20 22 25 28 32 36 40	10.8	0.8	4.2	4.4
	5	10 12 14 16 18 20 22 25 28 32 36 40 45 50	17.25	1	5.2	5.4
	6	12 14 16 18 20 22 25 28 32 36 40 45 50 56	24.83	1.2	6.2	6.4
	8	16 18 20 22 25 28 32 36 40 45 50 56 63 70 80	44.13	1.6	8.3	8.6
	10	18 20 22 25 28 32 36 40 45 50 56 63 70 80 90 100	68.94	2	10.3	10.6

▲ TXBH型号只有D2 ~ D6尺寸, D为图中D1,D2,D3的平均值。

▲ E为双重剪切负载最小值, T为参考值。