



# Ordering Leaflet

Alfa Laval Tubes

Tubes of manufacturing lengths of approx 6 meters  
 Product code: 5102  
 According to standard: ISO 2037

Finish: BD and BC

| Material Item No.                                    | PPL EUR | Material Item No. | PPL EUR | Size mm | Dimension (mm) OD/ID x t |  |
|--|---------|-------------------|---------|---------|--------------------------|--|
| <b>1.4307 (304L)</b>                                 |         |                   |         |         |                          |  |
| <b>1.4404 (316L)</b>                                 |         |                   |         |         |                          |  |
| 9611819010   | *       | 9611819210        | *       | 25.00   | 25.00/22.60x1.20         |  |
| 9611819030   | *       | 9611819230        | *       | 38.00   | 38.00/35.60x1.20         |  |
| 9611819060   | *       | 9611819260        | *       | 51.00   | 51.00/48.60x1.20         |  |
| 9611819090   | *       | 9611819280        | *       | 63.50   | 63.50/60.30x1.60         |  |
| 9611819101   | *       | 9611819290        | *       | 76.10   | 76.10/72.90x1.60         |  |
| 9611819120   | *       | 9611819310        | *       | 101.60  | 101.60/97.60x2.00        |  |
| <b>BC finish Inch tubes ISO 2037</b>                 |         |                   |         |         |                          |  |
| 9611819008   | *       | 9611819868        | *       | 25.00   | 25.00/22.60x1.20         |  |
| 9611819863   | *       | 9611819870        | *       | 38.00   | 38.00/35.60x1.20         |  |
| 9611819864   | *       | 9611819871        | *       | 51.00   | 51.00/48.60x1.20         |  |
| 9611819865   | *       | 9611819872        | *       | 63.50   | 63.50/60.30x1.60         |  |
| 9611819866   | *       | 9611819873        | *       | 76.10   | 76.10/72.90x1.60         |  |
| 9611819867   | *       | 9611819874        | *       | 101.60  | 101.60/97.60x2.00        |  |
| <b>BD finish Inch tubes ISO 2037 H3 execution**</b>  |         |                   |         |         |                          |  |
| 9614042502   | *       | 9614042509        | *       | 25.00   | 25.00/22.60x1.20         |  |
| 9614042504   | *       | 9614042511        | *       | 38.00   | 38.00/35.60x1.20         |  |
| 9614042505   | *       | 9614042512        | *       | 51.00   | 51.00/48.60x1.20         |  |
| 9614042506   | *       | 9614042513        | *       | 63.50   | 63.50/60.30x1.60         |  |
| 9614042507   | *       | 9614042514        | *       | 76.10   | 76.10/72.90x1.60         |  |
| 9614042508   | *       | 9614042515        | *       | 101.60  | 101.60/97.60x2.00        |  |
| <b>BC finish Inch tubes ISO 2037, H3 execution**</b> |         |                   |         |         |                          |  |
| 9614042501   | *       | 9614042522        | *       | 25.00   | 25.00/22.60x1.20         |  |
| 9614042517   | *       | 9614042524        | *       | 38.00   | 38.00/35.60x1.20         |  |
| 9614042518   | *       | 9614042525        | *       | 51.00   | 51.00/48.60x1.20         |  |
| 9614042519   | *       | 9614042526        | *       | 63.50   | 63.50/60.30x1.60         |  |
| 9614042520   | *       | 9614042527        | *       | 76.10   | 76.10/72.90x1.60         |  |
| 9614042521   | *       | 9614042528        | *       | 101.60  | 101.60/97.60x2.00        |  |

\* PPL prices per meter are updated monthly

\*\* H3 execution = Inside surface texture (Ra μm) including welded area ≤ 0.8 (EHEDG certified)

Please contact your Alfa Laval contact person for further information.

Alfa Laval reserves the right to change specifications without prior notification.

---

**How to contact Alfa Laval**

Contact details for all countries  
are continually updated on our website.  
Please visit [www.alfalaval.com](http://www.alfalaval.com) to  
access the information direct.