

# Floor Standing Enclosures

## EMC Range

### Accessories

## EMC Filter fans, EFE

- Description:** EMC capable filter fan. Special EMC screen in combination with stainless steel contact strips guarantee good contact with enclosure surface. Cutting edge surface of the enclosure needs to be blank for contact. Long service life.
- Approvals:** CE, GOST, UR, cUL.
- Material:** Plastic, UL 94-V0. EMC screen: stainless steel, contact strips.
- Pack quantity:** 1 fan with filter.

IP	Power (W)	Cut out dim.	Air flow m <sup>3</sup> /h	Filter	Item no.
54	19	126.5 x 126.5	61	44	EFE200R5
54	19	178 x 178	110	82	EFE220R5
54	19	224 x 224	156	116	EFE250R5
54	45	224 x 224	256	231	EFE300R5
54	115	292 x 292	480	370	EFE500R5
54	115	292 x 292	640	445	EFE600R5
54	169	292 x 292	845	560	EFE700R5

Air flow = Free air flow (m<sup>3</sup>/h).

Filter = Air flow filter fan + exhaust filter (m<sup>3</sup>/h).



## EMC Exhaust filter, EFAE

- Description:** Suitable for specific EMC enclosures. Cutting edge surface of the enclosure needs to be blank for contact.
- Material:** Plastic, UL94-V0. EMC screen: stainless steel, contact strips.
- Approvals:** CE, GOST, UR, cUL.
- Protection:** IP 54.
- Pack quantity:** 1 filter with housing.

IP	Cut out dim.	Item no.
54	126.5 x 126.5	EFAE200R5
54	178 x 178	EFAE220R5
54	224 x 224	EFAE250-300R5
54	292 x 292	EFAE500-700R5

IP 55 models on request: UV resistant.

