

Thermal Management

Heating & Anticondensation Range

Accessories

Anti condensation small heater, EGK

- Description:** Small semiconductor heater to be fixed in vertical position to prevent condensation. Mounting clip for 35 mm DIN rail (EN60715).
- Heating element:** PTC resistor, self regulating and temperature limiting.
- Material:** Plastic, and anodised aluminium profile.
- Operating temperature:** -45 to +70°C. The heating capacity is for ambient temperature 20°C.
- Connection:** 3x0.5 mm² (300 mm) silicon cable. For UL heaters 3XAWG20 (300 mm) cable.
- Protection:** IP 44, Class I (earthed).
- Approvals:** CE, EAC, cULus_UL Listed.
- Pack quantity:** 1 piece.

Capacity (W)	Starting current (A)	L (mm)	Voltage (V)	Item no.
10	1.0	52	120-240V AC/DC	EGK010
20	2.5	60	120-240V AC/DC	EGK020
30	3.0	70	120-240V AC/DC	EGK030

* The min / max voltage values for 120-240 V heaters are 110 / 265 V, operating with voltages below 140 V AC/DC reduces heating performance by approx. 10%.

