

符合DIN 59350带有加工余量的精密扁钢和精密方钢

2923.2363.




材料:

1.2363 / X 100 CrMoV 5-1

冷锻模钢

结构:

厚度已精磨, 宽度已打磨或铣削, 长度已加工



2923.2363. 符合DIN 59350带有加工余量的精密扁钢和精密方钢

s	8.2	10.4	12.4	15.4	20.4	25.4	30.4	40.4	50.4	60.4	80.4	100.4
b												
20.4					●							
25.3	●	●	●									
25.4						●						
30.3	●	●	●	●	●							
30.4							●					
40.3	●	●	●	●	●	●	●					
40.4								●				
50.3	●	●	●	●	●	●	●					
50.4									●			
60.3	●	●	●	●	●	●	●	●				
60.4										●		
80.3	●	●	●	●	●	●	●	●				
80.4											●	
100.3	●	●	●	●	●	●	●	●				
100.4												●
125.3		●	●	●	●	●	●	●				
150.3		●	●	●	●	●	●	●				
200.3		●	●	●	●	●	●	●				
250.3					●	●	●	●				

订购示例:

符合DIN 59350带有加工余量的精密扁钢和精密方钢	=	2923.2363.
宽 B	30.3 mm =	030.
厚度 S	8.2 mm =	008.
长度 L	1000 mm =	1000
订购编号	=	2923.2363. 030. 008. 1000