



lifgo SVZ Zahnstange		Einheit	5.0	5.1	5.3	5.4
	A	mm	23	27	48	68
	A1	mm	21	25	46	66
	B	mm	M10	M12	M20	M24
	C	mm	20	25	35	40
	D	mm	26	31,5	48,5	48,5
	E	mm	16	18,5	26,5	26,5
	F	mm				
	G	mm				
	H	mm				
	I	mm				
	J	mm				
	K	mm				
Zahnstangenlänge	L	mm	$L = Z \times tt$			
	M	mm				
	N	mm				
	O	mm				
	P	mm				
	R	mm				
	S	mm				
	T	mm				
	U	mm				
	V	mm				
	W	mm				
Anzahl Zähne	Z		nach Kundenangabe			
Modul	mt		1,10	2,46875	2,47917	2,48438
Zahnteilung	tt	mm	$tt = mt \times \text{Pi}$			
			3,45575	7,75580	7,78854	7,80491
Trägheitsmoment	lx	mm ⁴	16411	22961	253179	428881
Trägheitsmoment	ly	mm ⁴	24216	35018	297984	809895
Polares Trägheitsmoment	lp	mm ⁴	40628	57979	551164	1238776
Gewicht		Kg/m	3,65	4,84	14,45	21,61