


外形尺寸图

基本型


MY3B15~40



型号	A	B	C	CC	D	E	F	G	H	I	J	K	L	MM	N	NA	NN	R	S	T	V
MY3B15	4	35	14	—	16.6	2	10	5.5	13	—	6	11	57	M4×0.7	11	17	M10×1	—	83	8	—
MY3B20	8	36	26	—	21.6	2	13	7.5	20	28	6	8	66	M4×0.7	18	24	M20×1.5	12	106	10	—
MY3B25	8	46	32	—	26.4	2	13	7.5	20.5	34	8	10	70	M5×0.8	18.5	30	M26×1.5	15	111	10	—
MY3B32	8	60	32	—	33.6	2	16	8	22	40	8	15	80	M6×1	20	36	M26×1.5	18	124	13	—
MY3B40	10	70	41	—	41.6	3	16	11	29	50	10	16	92	M6×1	26	46	M32×2	23	150	13	—

型号	W	X	Y	ZZ	P(配管通口)		
					无记号	TN	TF
MY3B15	35	19	—	103	M5×0.8	—	—
MY3B20	50	25	—	132	Rc1/8	NPT1/8	G1/8
MY3B25	50	30	—	137	Rc1/8	NPT1/8	G1/8
MY3B32	50	40	—	156	Rc1/8	NPT1/8	G1/8
MY3B40	60	40	—	182	Rc1/4	NPT1/4	G1/4

安装用螺母 / 含在包装中(2个)。



零件号	适合缸径 (mm)	d	H	B	C
GMA-C-M10-1-4-14	15	M10×1.0	4	14	16.2
GMA-C-M20-1.5-8-26	20	M20×1.5	8	26	30
GMA-C-M26-1.5-8-32	25, 32	M26×1.5	8	32	37
GMA-C-M32-2-10-41	40	M32×2.0	10	41	47.3