

配件螺丝\ F型夹钳

code
5天发货

定位零件

选型指南

举例

型号

TC-CC56212

■橡胶头螺丝



型号	规格
TC-FG042507	M4X25 P=0.7
TC-FG044207	M4X42 P=0.7
TC-FG064410	M6X44 P=1.0
TC-FG086312	M8X63 P=1.25
TC-FC108515	M10X85 P=1.5
TC-FC121017	M12X100 P=1.75
TC-FC10138	10-24x1-3/8
TC-FC14134	1/4-20x1-3/4
TC-FC14218	1/4-20x2-1/8
TC-FC56212	5/16-18x2-1/2
TC-FC56300	5/16-18x3
TC-FC38312	3/8-16x3-1/2
TC-FC38412	3/8-16x4-1/2

■自动调心式螺丝



型号	规格
TC-SF05035	M5x35 P=0.8
TC-SF06050	M6x50 P=1.0
TC-SF08065	M8x65 P=1.25
TC-SF10085	M10x85 P=1.5
TC-SF12100	M12x100 P=1.75
TC-SF16150	M16x150 P=2.0
TC-SF14214	1/4-24X2-1/4
TC-SF56234	5/16-18X2-3/4
TC-SF38300	3/8-16X3
TC-SF12400	1/2-13X4

■锥形橡胶头螺丝



型号	规格
TC-CC10138	10-24X1-3/8
TC-CC14134	1/4-20x1-3/4
TC-CC14218	1/4-20x2-1/8
TC-CC56212	5/16-18x2-1/2
TC-CC38312	3/8-16x3-1/2

■标准螺丝



型号	规格
TC-SA041507	M4×15 P=0.7
TC-SA042007	M4×20 P=0.7
TC-SA042507	M4×25 P=0.7
TC-SA044007	M4×40 P=0.7
TC-SA051508	M5×15 P=0.8
TC-SA053008	M5×30 P=0.8
TC-SA064010	M6×40 P=1.0
TC-SA065010	M6×50 P=1.0
TC-SA083012	M8×30 P=1.25
TC-SA085012	M8×50 P=1.25
TC-SA085612	M8×56 P=1.25
TC-SA105015	M10×50 P=1.5
TC-SA107515	M10×75 P=1.5
TC-SA109015	M10×90 P=1.5
TC-SA185025	M18×50 P=2.5
TC-SA08034	8-32×3/4
TC-SA10118	10-24×1-1/8
TC-SA14112	1/4-20×1-1/2
TC-SA14134	1/4-20×1-3/4
TC-SA56200	5/16-18×2
TC-SA56212	5/16-18×2-1/2
TC-SA38300	3/8-16×3
TC-SA38400	3/8-16×4
TC-SA12300	1/2-13×3
TC-SA12412	1/2-13×4-1/2
TC-SA58500	5/8-11×5

■经济型F夹



- T型手柄
- 本体表面镀铬
- 螺杆发黑处理

型号	跨距×喉深 (mm)	型钢 (mm)	夹持力 (KG)
TC-UD45M	115x83	16x8	210
TC-UD65M	165x83	16x8	210
TC-UD85M	215x83	16x8	210
TC-UG85M	215x120	25x12	550
TC-UG125M	320x120	25x12	550
TC-UG165M7	420x178	26x12	450
TC-UG205M7	520x178	26x12	450

■重力型F夹



- T型手柄
- 可调换浮动压脚
- 本体表面镀铬
- 螺杆发黑处理

型号	跨距×喉深 (mm)	型钢 (mm)	自重 (KG)
TC-UM85M	215x140	30x14	2.7
TC-UM105M	265x140	30x14	2.9
TC-UM125M	320x140	30x14	3.1
TC-UM165M	420x140	30x14	3.5
TC-UM205M	520x140	30x14	3.9
TC-UM315M	800x140	30x14	4.9
TC-UM420M	1080x140	30x14	5.4

■超重力型F夹



- T型手柄
- 可调换浮动压脚
- 本体表面镀铬
- 螺杆发黑处理

型号	跨距×喉深 (mm)	型钢 (mm)	自重 (KG)
TC-UP125M	320x178	42x19	5.9
TC-UP165M	420x178	42x19	6.5
TC-UP205M	520x178	42x19	7.0
TC-UP245M	622x178	42x19	7.8
TC-UP315M	800x178	42x19	8.8
TC-UP420M	1030x178	42x19	10.0

缓冲器

手动滑台

千分尺
旋钮

简易
调整组件

柱塞

肘夹

夹紧组件

定位导向
零件

精密
定位销

定位销
衬套