

Network/server enclosures TS IT



IT power Page 63 IT cooling Page 81 IT monitoring Page 97 System accessories Cat. 34, Page 507

Material:

- Sheet steel
- Aluminium

Surface finish:

- Enclosure frame: Dipcoat-primed
- Interior installation: Dipcoat-primed
- Doors and roof: Dipcoat-primed, powder-coated

Colour:

- Enclosure frame and panels: RAL 7035

Protection category IP to IEC 60 529:

- IP 55 only in conjunction with baying seal or screw-fastened side panels

Supply includes:

- TS 8 enclosure frame with doors and roof plate
- Glazed aluminium door at the front (180°)
- Sheet steel door at the rear, 180° hinges
- Lock front and rear: Comfort handle for semi-cylinders and security lock 3524 E
- Roof plate, one-piece, solid
- Base tray and gland plate, multi-piece, solid
- Baying seal and sealing kit for gland plates (supplied loose)
- Connection accessories for potential equalisation with earthing point (supplied loose)

Note:

- Depending on the siting type and location, the door opening may vary for selected applications
- For enclosures with width and depth 2000 x 1200 / 2200 x 1000 / 2200 x 1200, the matching side panels are optionally available and are supplied fitted to the enclosure

Approvals:

- UL
- cUL

with glazed door, IP 55, empty enclosure

Width mm	Packs of	600	600	600	600	600	Cat. 34, Page
Height mm		800	1200	1800	2000	1800	
Depth mm		600	600	600	600	800	
Model No.	1 pc(s).	5525.790	5526.790	5527.790	5529.790	5528.790	
Accessories							
Side panels, screw-fastened, sheet steel	2 pc(s).	8173.235	8170.235	8186.235	8106.235	8188.235	534
Baying connector, external	6 pc(s).	8800.490	8800.490	8800.490	8800.490	8800.490	544
Base/plinth		from page	from page	from page	from page	from page	510
Cable route	1 pc(s).	-	-	-	5502.120	-	672
C rails, for depth	4 pc(s).	7828.060	7828.060	7828.060	7828.060	7828.080	613
C rails, for width	4 pc(s).	7828.060	7828.060	7828.060	7828.060	7828.060	613
Cable clamp rails, for depth	4 pc(s).	7828.062	7828.062	7828.062	7828.062	7828.082	669
Cable clamp rails, for width	4 pc(s).	7828.062	7828.062	7828.062	7828.062	7828.062	669
Component shelf for frame attachment	1 pc(s).	7165.035	7165.035	7165.035	7165.035	7166.735	627
19" installation		from page	from page	from page	from page	from page	678
Swing frame		from page	from page	from page	from page	from page	678
Partial mounting plates		from page	from page	from page	from page	from page	596

Network/server enclosures TS IT

with glazed door, IP 55, empty enclosure

Width mm	Packs of	600	600	600	600	Cat. 34, Page
Height mm		2000	2200	2000	2200	
Depth mm		800	800	1000	1000	
Model No.	1 pc(s).	5530.790	5531.790	5508.790	5513.790	

Accessories						
Side panels, screw-fastened, sheet steel	2 pc(s).	8108.235	8128.235	8100.235	–	534
Baying connector, external	6 pc(s).	8800.490	8800.490	8800.490	8800.490	544
Base/plinth		from page	from page	from page	from page	510
Cable route	1 pc(s).	5502.120	5502.120	5502.120	5502.120	672
C rails, for depth	4 pc(s).	7828.080	7828.080	7828.100	7828.100	613
C rails, for width	4 pc(s).	7828.060	7828.060	7828.060	7828.060	613
Cable clamp rails, for depth	4 pc(s).	7828.082	7828.082	7828.102	7828.102	669
Cable clamp rails, for width	4 pc(s).	7828.062	7828.062	7828.062	7828.062	669
Component shelf for frame attachment	1 pc(s).	7166.735	7166.735	7166.735	7166.735	627
19" installation		from page	from page	from page	from page	678
Swing frame		from page	from page	from page	from page	678
Partial mounting plates		from page	from page	from page	from page	596

with glazed door, IP 55, empty enclosure

Width mm	Packs of	600	600	800	800	Cat. 34, Page
Height mm		2000	2200	2000	1200	
Depth mm		1200	1200	600	800	
Model No.	1 pc(s).	5510.790	5515.790	5506.790	5503.790	

Accessories						
Side panels, screw-fastened, sheet steel	2 pc(s).	–	–	8106.235	8175.235	534
Baying connector, external	6 pc(s).	8800.490	8800.490	8800.490	8800.490	544
Base/plinth		from page	from page	from page	from page	510
Cable route	1 pc(s).	5502.120	5502.120	5502.120	–	672
C rails, for depth	4 pc(s).	7828.120	7828.120	7828.060	7828.080	613
C rails, for width	4 pc(s).	7828.060	7828.060	7828.080	7828.080	613
Cable clamp rails, for depth	4 pc(s).	7828.122	7828.122	7828.062	7828.082	669
Cable clamp rails, for width	4 pc(s).	7828.062	7828.062	7828.082	7828.082	669
Component shelf for frame attachment	1 pc(s).	7166.735	7166.735	7185.035	7186.735	627
19" installation		from page	from page	from page	from page	678
Swing frame		from page	from page	from page	from page	678
Partial mounting plates		from page	from page	from page	from page	596

with glazed door, IP 55, empty enclosure

Width mm	Packs of	800	800	800	800	Cat. 34, Page
Height mm		1800	2000	2200	1200	
Depth mm		800	800	800	1000	
Model No.	1 pc(s).	5505.790	5507.790	5512.790	5504.790	

Accessories						
Side panels, screw-fastened, sheet steel	2 pc(s).	8188.235	8108.235	8128.235	8176.235	534
Baying connector, external	6 pc(s).	8800.490	8800.490	8800.490	8800.490	544
Base/plinth		from page	from page	from page	from page	510
Cable route	1 pc(s).	–	5502.120	5502.120	–	672
C rails, for depth	4 pc(s).	7828.080	7828.080	7828.080	7828.100	613
C rails, for width	4 pc(s).	7828.080	7828.080	7828.080	7828.080	613
Cable clamp rails, for depth	4 pc(s).	7828.082	7828.082	7828.082	7828.102	669
Cable clamp rails, for width	4 pc(s).	7828.082	7828.082	7828.082	7828.082	669
Component shelf for frame attachment	1 pc(s).	7186.735	7186.735	7186.735	7186.735	627
19" installation		from page	from page	from page	from page	678
Swing frame		from page	from page	from page	from page	678
Partial mounting plates		from page	from page	from page	from page	596

Network/server enclosures TS IT

with glazed door, IP 55, empty enclosure

Width mm	Packs of	800	800	800	800	Cat. 34, Page
Height mm		2000	2200	2000	2200	
Depth mm		1000	1000	1200	1200	
Model No.	1 pc(s).	5509.790	5514.790	5511.790	5516.790	

Accessories						
Side panels, screw-fastened, sheet steel	2 pc(s).	8100.235	–	–	–	534
Baying connector, external	6 pc(s).	8800.490	8800.490	8800.490	8800.490	544
Base/plinth		from page	from page	from page	from page	510
Cable route	1 pc(s).	5502.120	5502.120	5502.120	5502.120	672
C rails, for depth	4 pc(s).	7828.100	7828.100	7828.120	7828.120	613
C rails, for width	4 pc(s).	7828.080	7828.080	7828.080	7828.080	613
Cable clamp rails, for depth	4 pc(s).	7828.102	7828.102	7828.122	7828.122	669
Cable clamp rails, for width	4 pc(s).	7828.082	7828.082	7828.082	7828.082	669
Component shelf for frame attachment	1 pc(s).	7186.735	7186.735	7186.735	7186.735	627
19" installation		from page	from page	from page	from page	678
Swing frame		from page	from page	from page	from page	678
Partial mounting plates		from page	from page	from page	from page	596

