

Support strips

For attachment of

- Cable ducts
- Cable conduit holders
- Contact hazard protection covers
- Equipment installed on the door
- Cable clamping and attachment

4.5 mm diameter hole on a 25 mm DIN pitch pattern

Material:

- Sheet steel

Surface finish:

- Zinc-plated

Supply includes:

- Assembly parts



Accessories:

- Screws and self-tapping screws M5, see page 625

For TS, SE, CM, TP

For door width mm	Length mm	Packs of	Model No.
400	290	20 pc(s).	4594.000
500	390	20 pc(s).	4309.000
600	490	20 pc(s).	4596.000
800	690	20 pc(s).	4598.000
900	790	20 pc(s).	4579.000
1000	890	20 pc(s).	4599.000

For AE

For enclosures AE	Packs of	Model No.
1018.600 ²⁾ , 1019.500 ²⁾ 1050.500 ¹⁾ , 1057.500 1100.500, 1110.500 1114.500 ¹⁾ , 1130.500 1213.500 ¹⁾ , 1350.500 ¹⁾	20 pc(s).	2325.000
1009.600 ²⁾ , 1376.500 1012.500 ²⁾ , 1039.500 1054.500, 1058.500 1060.500, 1076.500 1090.500, 1260.500 ¹⁾ 1339.500, 1360.500	20 pc(s).	2326.000
1014.500 ²⁾ , 1073.500 1077.500	20 pc(s).	2327.000
1016.500 ²⁾ , 1017.500 ²⁾ 1055.500, 1180.500 1280.500 ¹⁾	20 pc(s).	2328.000

¹⁾For these AE models, the door rails should be cut to length at the knockout.

²⁾Only in conjunction with perforated mounting strips (see page 576)

Spacers

The universal assembly component for all situations where a distance from the mounting level is required. With self-tapping thread for diameter 4.5 mm. The following components may be attached to the rear using 5.5 x 13 mm screws:

- Top-hat/cross rails
 - Contact hazard protection covers
 - Master switch trim panels
 - Cable clamp rails
- etc.

Material:

- Hexagonal steel (SW8)

Surface finish:

- Zinc-plated



Accessories:

- Screws 5.5 x 13 mm, see page 625

Length mm	Packs of	Model No.
25	12 pc(s).	2311.225
50	12 pc(s).	2311.250

