


## SERIES 61



### INJECTION POLYURETHANE WHEELS, POLYAMIDE 6 CENTRE, SWIVEL BRACKET WITH STEM TYPE "NL"

#### Wheel description




**Tread:** injection polyurethane tread, hardness 80 Shore A; excellent rolling resistance and elasticity, highly resistant to wear and to tearing.

**Centre:** polyamide 6.

**Hub:** the hub is available with plain bearing and with roller bearing..

#### Bracket description



#### Standard duty bracket type NL (max. carrying capacity 400 daN)

- 1) **Plate:** electrolytically galvanised steel plate
  - 2) **Fork:** electrolytically galvanised steel plate
  - 3) **Ball Racing Ring:** electrolytically galvanised steel plate
  - 4) **King Pin:** incorporated in top plate and cold riveted
  - 5) **Swivel actions:** double ring of greased balls
- Finishing:** electrolytic galvanisation  
**Fitting:** stem