

SERIES 68

POLYAMIDE 6 SOLID WHEELS



Wheel description

Polyamide 6 solid wheels.

Hub

The hub is available with plain bearing, with roller bearing, with stainless steel roller bearing, with ball bearing and with ball bearing facilities.

Diameters: 65-250 mm

Carrying capacity: 120-1200 daN

Fittings with swivel, fixed and swivel with brake brackets



Standard duty brackets type NL - NLX

Max. carrying capacity 400 daN – available diameters 80-300 mm

Models available: with top plate fastening, with bolt hole

Suitable brakes: front-locking and central (hexagonal) brake systems



Medium duty brackets type M

Max. carrying capacity 500 daN – available diameters 150-200 mm

Models available: with top plate fastening

Suitable brakes: adjustable front-locking brake



Medium-heavy duty brackets type P - PX

Max. carrying capacity 750 daN – available diameters 80-200 mm

Models available: with top plate fastening

Suitable brakes: front-locking and adjustable rear-locking brake systems



Electro-welded brackets type EE HD

Max. carrying capacity 2500 daN – available diameters 150-300 mm

Top plate fastening. Adjustable rear-locking brake systems

Uses

Environments

Suitable for humid environment with harsh chemicals; not suitable for applications where concentrated organic acids or strong mineral acids are present.

Usage temperatures: from -30°C to +80°C

Floors



Handling

