

## TWIN 36 SERIES

### TWIN THERMOPLASTIC POLYURETHANE WHEELS WITH POLYAMIDE 6 CENTER



#### Wheel description

Thermoplastic polyurethane

#### Hub

The hub is available with plain bore

**Diameters:** 40-60 mm

**Carrying capacity:** 40-140 daN

### Fittings with brackets



#### Swivel top plate brackets

Top carrying capacity 140 daN  
Diameters available 40 – 60 mm



#### Swivel bolt hole brackets

Top carrying capacity 140 daN  
Diameters available 40 – 60 mm



#### Swivel brackets with stem

Top carrying capacity 140 daN  
Diameters available 40 – 60 mm

### Uses

#### Environments

Suitable for humid environments with harsh chemicals; not suitable for applications where concentrated organic acids or strong mineral acids are present; is used for home and institutional applications, with light and standard carrying capacity.

Typical usage: office furniture, shelves, display stands.

Usage temperatures: from -5°C to +40°C

#### Floors



#### Handling

