

Gimbal joint DN 30

Oper. pressure [bar]: 25

Oper. temp. range [K]: 4 ÷ 310

Oper. travel ranges (max.)
- angular [°] : ± 10

Weight (max) [Kg] : 0.5

Spring rates (max.)
- angular [N m/°] : 0.5

Operating fluids : LO2, LH2, LHe,
GHe

Bellows material : AISI 316 L

Application : A5 EPC CFC lines

Status : Qualified for flight

