



★ 产品特点:加大了与安装部的摩擦,可起到防止松动的作用。

精度	类型		M材质	S表面处理
	B尺寸固定型	B尺寸指定型		
普通级	MWAAG	MWAAE	一般结构用钢	四氧化三铁保护膜
	MWBAG	MWBAE		无电解镀锌
	MWEAG	MWEAE	不锈钢	-

⚠ 如对防锈有要求,请优先选用不锈钢材质或无电解镀锌产品。

$D \leq 16 \ C < 0.2$   
 $D \geq 20 \ C < 0.5$   
 $D \leq 16 \ C < 0.2$   
 $D \geq 20 \ C < 0.5$   
 $Q \begin{matrix} +0.3 \\ +0.1 \end{matrix}$   
 $D \begin{matrix} 0 \\ -0.2 \end{matrix}$   
 $B \pm 0.1$

视角标准: 第一视角



①代号 - ②D - ③Q - ④B  
 MWAAG - D4 - Q2 - B1

**B尺寸固定型(普通级)**

①代号	②D		③Q										④B								
MWAAG MWBAG MWEAG	4	2											1	2							
	5	2	3										1	2							
	6	2	3	4								1	2								
	8	2	3	4	5	6					1	2	3	5							
	10	2	3	4	5	6	8					1	2	3	5						
	12		3	4	5	6	8	10					1	2	3	5					
	13			4	5	6	8	10					1	2	3	5					
	14			4	5	6	8	10					1	2	3	5					
	15			4	5	6	8	10	12				1	2	3	5					
	16			4	5	6	8	10	12				1	2	3	5					
	20			4	5	6	8	10	12	15			2	3	5						
	25				6	8	10	12	15	16	20			2	3	5					
	30					8	10	12	15	16	20	25			2	3	5				
	35						10	12	15	16	20	25			3	5	10				
	40							10	12	15	16	20	25	30			3	5	10		
	50								10	12	15	16	20	25	30			3	5	10	
60									15	16	20	25	30			3	5	10			



①代号 - ②D - ③Q - ④B  
 MWAAE - D4 - Q2 - B1

**B尺寸指定型(普通级)**

①代号	②D	③Q										④B指定单位0.5mm							
MWAAE MWBAE MWEAE	4	2																	
	5	2	3																
	6	2	3	4															
	8	2	3	4	5	6													
	10	2	3	4	5	6	8												
	12		3	4	5	6	8	10											
	13			4	5	6	8	10											
	14			4	5	6	8	10					1.0 ~ 10.0						
	15			4	5	6	8	10	12										
	16			4	5	6	8	10	12										
	20			4	5	6	8	10	12	15	16								
	25					6	8	10	12	15	16	20							
30						8	10	12	15	16	20	25							



交货期 **1**天发货

数量分类	标准订单	特殊订单
	小单	大单
数量	1~200	201~
交货期	1天发货	另行报价

⚠ 常州工厂发货。  
 ⚠ 部分产品型号 7 天发货, 请以报价为准。

A6  
垫圈、轴环