

订购编号示例

1 代号
QC-FC-042507

33
快速夹钳

<p>橡胶压头</p>	<table border="1"> <thead> <tr> <th>1 代号</th> <th>螺杆直径</th> <th>螺距</th> <th>压头总长 L</th> </tr> </thead> <tbody> <tr><td>QC-FC-042507</td><td>M4</td><td>0.7</td><td>25</td></tr> <tr><td>QC-FC-044207</td><td>M4</td><td>0.7</td><td>42</td></tr> <tr><td>QC-FC-064410</td><td>M6</td><td>1</td><td>44</td></tr> <tr><td>QC-FC-064110</td><td>M6</td><td>1</td><td>51</td></tr> <tr><td>QC-FC-086312</td><td>M8</td><td>1.25</td><td>63</td></tr> <tr><td>QC-FC-087512</td><td>M8</td><td>1.25</td><td>75</td></tr> <tr><td>QC-FC-108515</td><td>M10</td><td>1.5</td><td>85</td></tr> <tr><td>QC-FC-121017</td><td>M12</td><td>1.75</td><td>100</td></tr> <tr><td>QC-FC-10138</td><td>3/16</td><td>每英寸 24 牙</td><td>1-3/8</td></tr> <tr><td>QC-FC-14134</td><td>1/4</td><td>每英寸 20 牙</td><td>1-3/4</td></tr> <tr><td>QC-FC-14218</td><td>1/4</td><td>每英寸 20 牙</td><td>2-1/8</td></tr> <tr><td>QC-FC-56212</td><td>5/16</td><td>每英寸 18 牙</td><td>2-1/2</td></tr> <tr><td>QC-FC-56300</td><td>5/16</td><td>每英寸 18 牙</td><td>3</td></tr> <tr><td>QC-FC-38312</td><td>3/8</td><td>每英寸 16 牙</td><td>3-1/2</td></tr> <tr><td>QC-FC-38412</td><td>3/8</td><td>每英寸 16 牙</td><td>4-1/2</td></tr> <tr><td>QC-FC-38334</td><td>3/8</td><td>每英寸 16 牙</td><td>3-3/4</td></tr> <tr><td>QC-FC-12334</td><td>1/2</td><td>每英寸 12 牙</td><td>3-3/4</td></tr> </tbody> </table>	1 代号	螺杆直径	螺距	压头总长 L	QC-FC-042507	M4	0.7	25	QC-FC-044207	M4	0.7	42	QC-FC-064410	M6	1	44	QC-FC-064110	M6	1	51	QC-FC-086312	M8	1.25	63	QC-FC-087512	M8	1.25	75	QC-FC-108515	M10	1.5	85	QC-FC-121017	M12	1.75	100	QC-FC-10138	3/16	每英寸 24 牙	1-3/8	QC-FC-14134	1/4	每英寸 20 牙	1-3/4	QC-FC-14218	1/4	每英寸 20 牙	2-1/8	QC-FC-56212	5/16	每英寸 18 牙	2-1/2	QC-FC-56300	5/16	每英寸 18 牙	3	QC-FC-38312	3/8	每英寸 16 牙	3-1/2	QC-FC-38412	3/8	每英寸 16 牙	4-1/2	QC-FC-38334	3/8	每英寸 16 牙	3-3/4	QC-FC-12334	1/2	每英寸 12 牙	3-3/4																																				
1 代号	螺杆直径	螺距	压头总长 L																																																																																																										
QC-FC-042507	M4	0.7	25																																																																																																										
QC-FC-044207	M4	0.7	42																																																																																																										
QC-FC-064410	M6	1	44																																																																																																										
QC-FC-064110	M6	1	51																																																																																																										
QC-FC-086312	M8	1.25	63																																																																																																										
QC-FC-087512	M8	1.25	75																																																																																																										
QC-FC-108515	M10	1.5	85																																																																																																										
QC-FC-121017	M12	1.75	100																																																																																																										
QC-FC-10138	3/16	每英寸 24 牙	1-3/8																																																																																																										
QC-FC-14134	1/4	每英寸 20 牙	1-3/4																																																																																																										
QC-FC-14218	1/4	每英寸 20 牙	2-1/8																																																																																																										
QC-FC-56212	5/16	每英寸 18 牙	2-1/2																																																																																																										
QC-FC-56300	5/16	每英寸 18 牙	3																																																																																																										
QC-FC-38312	3/8	每英寸 16 牙	3-1/2																																																																																																										
QC-FC-38412	3/8	每英寸 16 牙	4-1/2																																																																																																										
QC-FC-38334	3/8	每英寸 16 牙	3-3/4																																																																																																										
QC-FC-12334	1/2	每英寸 12 牙	3-3/4																																																																																																										
<p>橡胶锥形压头</p>	<table border="1"> <thead> <tr> <th>1 代号</th> <th>螺杆直径</th> <th>螺距</th> <th>压头总长 L</th> </tr> </thead> <tbody> <tr><td>QC-CC-10138</td><td>3/16</td><td>每英寸 24 牙</td><td>1-3/8</td></tr> <tr><td>QC-CC-14134</td><td>1/4</td><td>每英寸 20 牙</td><td>1-3/4</td></tr> <tr><td>QC-CC-14214</td><td>1/4</td><td>每英寸 20 牙</td><td>2-1/4</td></tr> <tr><td>QC-CC-14218</td><td>1/4</td><td>每英寸 20 牙</td><td>2-1/8</td></tr> <tr><td>QC-CC-56212</td><td>5/16</td><td>每英寸 18 牙</td><td>2-1/2</td></tr> <tr><td>QC-CC-56300</td><td>5/16</td><td>每英寸 18 牙</td><td>3</td></tr> <tr><td>QC-CC-38312</td><td>3/8</td><td>每英寸 16 牙</td><td>3-1/2</td></tr> </tbody> </table>	1 代号	螺杆直径	螺距	压头总长 L	QC-CC-10138	3/16	每英寸 24 牙	1-3/8	QC-CC-14134	1/4	每英寸 20 牙	1-3/4	QC-CC-14214	1/4	每英寸 20 牙	2-1/4	QC-CC-14218	1/4	每英寸 20 牙	2-1/8	QC-CC-56212	5/16	每英寸 18 牙	2-1/2	QC-CC-56300	5/16	每英寸 18 牙	3	QC-CC-38312	3/8	每英寸 16 牙	3-1/2																																																																												
1 代号	螺杆直径	螺距	压头总长 L																																																																																																										
QC-CC-10138	3/16	每英寸 24 牙	1-3/8																																																																																																										
QC-CC-14134	1/4	每英寸 20 牙	1-3/4																																																																																																										
QC-CC-14214	1/4	每英寸 20 牙	2-1/4																																																																																																										
QC-CC-14218	1/4	每英寸 20 牙	2-1/8																																																																																																										
QC-CC-56212	5/16	每英寸 18 牙	2-1/2																																																																																																										
QC-CC-56300	5/16	每英寸 18 牙	3																																																																																																										
QC-CC-38312	3/8	每英寸 16 牙	3-1/2																																																																																																										
<p>螺栓压头</p>	<table border="1"> <thead> <tr> <th>1 代号</th> <th>螺杆直径</th> <th>螺距</th> <th>螺杆长度 L</th> </tr> </thead> <tbody> <tr><td>QC-SA-041507</td><td>M4</td><td>0.7</td><td>15</td></tr> <tr><td>QC-SA-042007 (尼龙)</td><td>M4</td><td>0.7</td><td>20</td></tr> <tr><td>QC-SA-042507</td><td>M4</td><td>0.7</td><td>25</td></tr> <tr><td>QC-SA-044007</td><td>M4</td><td>0.7</td><td>40</td></tr> <tr><td>QC-SA-051508</td><td>M5</td><td>0.8</td><td>15</td></tr> <tr><td>QC-SA-053008</td><td>M5</td><td>0.8</td><td>30</td></tr> <tr><td>QC-SA-064010</td><td>M6</td><td>1</td><td>40</td></tr> <tr><td>QC-SA-065010</td><td>M6</td><td>1</td><td>50</td></tr> <tr><td>QC-SA-083012</td><td>M8</td><td>1.25</td><td>30</td></tr> <tr><td>QC-SA-085012</td><td>M8</td><td>1.25</td><td>50</td></tr> <tr><td>QC-SA-086512</td><td>M8</td><td>1.25</td><td>65</td></tr> <tr><td>QC-SA-105015</td><td>M10</td><td>1.5</td><td>50</td></tr> <tr><td>QC-SA-107515</td><td>M10</td><td>1.5</td><td>75</td></tr> <tr><td>QC-SA-109015</td><td>M10</td><td>1.5</td><td>90</td></tr> <tr><td>QC-SA-125017</td><td>M12</td><td>1.75</td><td>50</td></tr> <tr><td>QC-SA-08034 (尼龙)</td><td>5/32</td><td>每英寸 32 牙</td><td>3/4</td></tr> <tr><td>QC-SA-10118</td><td>3/16</td><td>每英寸 24 牙</td><td>1-1/8</td></tr> <tr><td>QC-SA-14112</td><td>1/4</td><td>每英寸 20 牙</td><td>1-1/2</td></tr> <tr><td>QC-SA-14134</td><td>1/4</td><td>每英寸 20 牙</td><td>1-3/4</td></tr> <tr><td>QC-SA-56200</td><td>5/16</td><td>每英寸 18 牙</td><td>2</td></tr> <tr><td>QC-SA-56212</td><td>5/16</td><td>每英寸 18 牙</td><td>2-1/2</td></tr> <tr><td>QC-SA-38300</td><td>3/8</td><td>每英寸 16 牙</td><td>3</td></tr> <tr><td>QC-SA-38400</td><td>3/8</td><td>每英寸 16 牙</td><td>4</td></tr> <tr><td>QC-SA-12300</td><td>1/2</td><td>每英寸 12 牙</td><td>3</td></tr> <tr><td>QC-SA-12412</td><td>1/2</td><td>每英寸 12 牙</td><td>4-1/2</td></tr> <tr><td>QC-SA-58500</td><td>5/8</td><td>每英寸 11 牙</td><td>5</td></tr> </tbody> </table>	1 代号	螺杆直径	螺距	螺杆长度 L	QC-SA-041507	M4	0.7	15	QC-SA-042007 (尼龙)	M4	0.7	20	QC-SA-042507	M4	0.7	25	QC-SA-044007	M4	0.7	40	QC-SA-051508	M5	0.8	15	QC-SA-053008	M5	0.8	30	QC-SA-064010	M6	1	40	QC-SA-065010	M6	1	50	QC-SA-083012	M8	1.25	30	QC-SA-085012	M8	1.25	50	QC-SA-086512	M8	1.25	65	QC-SA-105015	M10	1.5	50	QC-SA-107515	M10	1.5	75	QC-SA-109015	M10	1.5	90	QC-SA-125017	M12	1.75	50	QC-SA-08034 (尼龙)	5/32	每英寸 32 牙	3/4	QC-SA-10118	3/16	每英寸 24 牙	1-1/8	QC-SA-14112	1/4	每英寸 20 牙	1-1/2	QC-SA-14134	1/4	每英寸 20 牙	1-3/4	QC-SA-56200	5/16	每英寸 18 牙	2	QC-SA-56212	5/16	每英寸 18 牙	2-1/2	QC-SA-38300	3/8	每英寸 16 牙	3	QC-SA-38400	3/8	每英寸 16 牙	4	QC-SA-12300	1/2	每英寸 12 牙	3	QC-SA-12412	1/2	每英寸 12 牙	4-1/2	QC-SA-58500	5/8	每英寸 11 牙	5
1 代号	螺杆直径	螺距	螺杆长度 L																																																																																																										
QC-SA-041507	M4	0.7	15																																																																																																										
QC-SA-042007 (尼龙)	M4	0.7	20																																																																																																										
QC-SA-042507	M4	0.7	25																																																																																																										
QC-SA-044007	M4	0.7	40																																																																																																										
QC-SA-051508	M5	0.8	15																																																																																																										
QC-SA-053008	M5	0.8	30																																																																																																										
QC-SA-064010	M6	1	40																																																																																																										
QC-SA-065010	M6	1	50																																																																																																										
QC-SA-083012	M8	1.25	30																																																																																																										
QC-SA-085012	M8	1.25	50																																																																																																										
QC-SA-086512	M8	1.25	65																																																																																																										
QC-SA-105015	M10	1.5	50																																																																																																										
QC-SA-107515	M10	1.5	75																																																																																																										
QC-SA-109015	M10	1.5	90																																																																																																										
QC-SA-125017	M12	1.75	50																																																																																																										
QC-SA-08034 (尼龙)	5/32	每英寸 32 牙	3/4																																																																																																										
QC-SA-10118	3/16	每英寸 24 牙	1-1/8																																																																																																										
QC-SA-14112	1/4	每英寸 20 牙	1-1/2																																																																																																										
QC-SA-14134	1/4	每英寸 20 牙	1-3/4																																																																																																										
QC-SA-56200	5/16	每英寸 18 牙	2																																																																																																										
QC-SA-56212	5/16	每英寸 18 牙	2-1/2																																																																																																										
QC-SA-38300	3/8	每英寸 16 牙	3																																																																																																										
QC-SA-38400	3/8	每英寸 16 牙	4																																																																																																										
QC-SA-12300	1/2	每英寸 12 牙	3																																																																																																										
QC-SA-12412	1/2	每英寸 12 牙	4-1/2																																																																																																										
QC-SA-58500	5/8	每英寸 11 牙	5																																																																																																										
<p>螺栓平面压头</p>	<table border="1"> <thead> <tr> <th>1 代号</th> <th>螺杆直径</th> <th>螺距</th> <th>螺杆长度 L</th> </tr> </thead> <tbody> <tr><td>QC-SF-05035</td><td>M5</td><td>0.8</td><td>35</td></tr> <tr><td>QC-SF-06050</td><td>M6</td><td>1</td><td>50</td></tr> <tr><td>QC-SF-08065</td><td>M8</td><td>1.25</td><td>65</td></tr> <tr><td>QC-SF-10085</td><td>M10</td><td>1.5</td><td>85</td></tr> <tr><td>QC-SF-12100</td><td>M12</td><td>1.75</td><td>100</td></tr> <tr><td>QC-SF-16150</td><td>M16</td><td>2</td><td>150</td></tr> <tr><td>QC-SF-14214</td><td>1/4</td><td>每英寸 20 牙</td><td>2-1/4</td></tr> <tr><td>QC-SF-56234</td><td>5/16</td><td>每英寸 18 牙</td><td>2-3/4</td></tr> <tr><td>QC-SF-38300</td><td>3/8</td><td>每英寸 16 牙</td><td>3</td></tr> <tr><td>QC-SF-12400</td><td>1/2</td><td>每英寸 12 牙</td><td>4</td></tr> </tbody> </table>	1 代号	螺杆直径	螺距	螺杆长度 L	QC-SF-05035	M5	0.8	35	QC-SF-06050	M6	1	50	QC-SF-08065	M8	1.25	65	QC-SF-10085	M10	1.5	85	QC-SF-12100	M12	1.75	100	QC-SF-16150	M16	2	150	QC-SF-14214	1/4	每英寸 20 牙	2-1/4	QC-SF-56234	5/16	每英寸 18 牙	2-3/4	QC-SF-38300	3/8	每英寸 16 牙	3	QC-SF-12400	1/2	每英寸 12 牙	4																																																																
1 代号	螺杆直径	螺距	螺杆长度 L																																																																																																										
QC-SF-05035	M5	0.8	35																																																																																																										
QC-SF-06050	M6	1	50																																																																																																										
QC-SF-08065	M8	1.25	65																																																																																																										
QC-SF-10085	M10	1.5	85																																																																																																										
QC-SF-12100	M12	1.75	100																																																																																																										
QC-SF-16150	M16	2	150																																																																																																										
QC-SF-14214	1/4	每英寸 20 牙	2-1/4																																																																																																										
QC-SF-56234	5/16	每英寸 18 牙	2-3/4																																																																																																										
QC-SF-38300	3/8	每英寸 16 牙	3																																																																																																										
QC-SF-12400	1/2	每英寸 12 牙	4																																																																																																										
	<table border="1"> <thead> <tr> <th>1 代号</th> <th>配套螺杆直径</th> </tr> </thead> <tbody> <tr><td>QC-FW-080</td><td>M4</td></tr> <tr><td>QC-FW-100</td><td>M5</td></tr> <tr><td>QC-FW-140</td><td>1/4</td></tr> <tr><td>QC-FW-141</td><td>1/4</td></tr> <tr><td>QC-FW-516</td><td>5/16</td></tr> <tr><td>QC-FW-380</td><td>3/8</td></tr> <tr><td>QC-FW-120</td><td>1/2</td></tr> <tr><td>QC-FW-580</td><td>5/8</td></tr> </tbody> </table>	1 代号	配套螺杆直径	QC-FW-080	M4	QC-FW-100	M5	QC-FW-140	1/4	QC-FW-141	1/4	QC-FW-516	5/16	QC-FW-380	3/8	QC-FW-120	1/2	QC-FW-580	5/8																																																																																										
1 代号	配套螺杆直径																																																																																																												
QC-FW-080	M4																																																																																																												
QC-FW-100	M5																																																																																																												
QC-FW-140	1/4																																																																																																												
QC-FW-141	1/4																																																																																																												
QC-FW-516	5/16																																																																																																												
QC-FW-380	3/8																																																																																																												
QC-FW-120	1/2																																																																																																												
QC-FW-580	5/8																																																																																																												
	<table border="1"> <thead> <tr> <th>1 代号</th> <th>配套螺杆直径</th> </tr> </thead> <tbody> <tr><td>QC-BR-140</td><td>1/4</td></tr> <tr><td>QC-BR-141</td><td>1/4</td></tr> <tr><td>QC-BR-516</td><td>5/16</td></tr> <tr><td>QC-BR-380</td><td>3/8</td></tr> <tr><td>QC-BR-120</td><td>1/2</td></tr> <tr><td>QC-BR-580</td><td>5/8</td></tr> </tbody> </table>	1 代号	配套螺杆直径	QC-BR-140	1/4	QC-BR-141	1/4	QC-BR-516	5/16	QC-BR-380	3/8	QC-BR-120	1/2	QC-BR-580	5/8																																																																																														
1 代号	配套螺杆直径																																																																																																												
QC-BR-140	1/4																																																																																																												
QC-BR-141	1/4																																																																																																												
QC-BR-516	5/16																																																																																																												
QC-BR-380	3/8																																																																																																												
QC-BR-120	1/2																																																																																																												
QC-BR-580	5/8																																																																																																												