


# 夹钳压头与附件

橡胶压头



表一

橡胶锥形压头




表 2

螺栓压头




表 3

螺栓平面压头




表 4

螺栓压片



Part No. Description

表 5

实心夹夹板



表 6

## 订购编号示例

①代号

QCF-FC-042507

■ 表一

①代号	螺杆直径	螺距	螺杆长度 L
QCF-FC-042507	M4	0.7	25
QCF-FC-044207	M4	0.7	42
QCF-FC-064410	M6	1	44
QCF-FC-064110	M6	1	51
QCF-FC-086312	M8	1.25	63
QCF-FC-087512	M8	1.25	75
QCF-FC-108515	M10	1.5	85
QCF-FC-121017	M12	1.75	100
QCF-FC-10138	3/16	每英寸 24 牙	1-3/8
QCF-FC-14134	1/4	每英寸 20 牙	1-3/4
QCF-FC-14218	1/4	每英寸 20 牙	2-1/8
QCF-FC-56212	5/16	每英寸 18 牙	2-1/2
QCF-FC-56300	5/16	每英寸 18 牙	3
QCF-FC-38312	3/8	每英寸 16 牙	3-1/2
QCF-FC-38412	3/8	每英寸 16 牙	4-1/2
QCF-FC-38334	3/8	每英寸 16 牙	3-3/4
QCF-FC-12334	1/2	每英寸 12 牙	3-3/4

■ 表 2

①代号	螺杆直径	螺距	螺杆长度 L
QCF-CC-10138	3/16	每英寸 24 牙	1-3/8
QCF-CC-14134	1/4	每英寸 20 牙	1-3/4
QCF-CC-14214	1/4	每英寸 20 牙	2-1/4
QCF-CC-14218	1/4	每英寸 20 牙	2-1/8
QCF-CC-56212	5/16	每英寸 18 牙	2-1/2
QCF-CC-56300	5/16	每英寸 18 牙	3
QCF-CC-38312	3/8	每英寸 16 牙	3-1/2

■ 表 3

①代号	螺杆直径	螺距	螺杆长度 L
QCF-SA-041507	M4	0.7	15
QCF-SA-042007(尼龙)	M4	0.7	20
QCF-SA-042507	M4	0.7	25
QCF-SA-044007	M4	0.7	40
QCF-SA-051508	M5	0.8	15
QCF-SA-053008	M5	0.8	30
QCF-SA-064010	M6	1	40
QCF-SA-065010	M6	1	50
QCF-SA-083012	M8	1.25	30
QCF-SA-085012	M8	1.25	50
QCF-SA-086512	M8	1.25	65
QCF-SA-105015	M10	1.5	50
QCF-SA-107515	M10	1.5	75
QCF-SA-109015	M10	1.5	90
QCF-SA-125017	M12	1.75	50
QCF-SA-08034(尼龙)	5/32	每英寸 32 牙	3/4
QCF-SA-10118	3/16	每英寸 24 牙	1-1/8
QCF-SA-14112	1/4	每英寸 20 牙	1-1/2
QCF-SA-14134	1/4	每英寸 20 牙	1-3/4
QCF-SA-56200	5/16	每英寸 18 牙	2
QCF-SA-56212	5/16	每英寸 18 牙	2-1/2
QCF-SA-38300	3/8	每英寸 16 牙	3
QCF-SA-38400	3/8	每英寸 16 牙	4
QCF-SA-12300	1/2	每英寸 12 牙	3
QCF-SA-12412	1/2	每英寸 12 牙	4-1/2
QCF-SA-58500	5/8	每英寸 11 牙	5

■ 表 4

①代号	螺杆直径	螺距	螺杆长度 L
QCF-SF-05035	M5	0.8	35
QCF-SF-06050	M6	1	50
QCF-SF-08065	M8	1.25	65
QCF-SF-10085	M10	1.5	85
QCF-SF-12100	M12	1.75	100
QCF-SF-16150	M16	2	150
QCF-SF-14214	1/4	每英寸 20 牙	2-1/4
QCF-SF-56234	5/16	每英寸 18 牙	2-3/4
QCF-SF-38300	3/8	每英寸 16 牙	3
QCF-SF-12400	1/2	每英寸 12 牙	4

■ 表 5

①代号	配套螺杆直径
QCF-FW-080	
QCF-FW-100	
QCF-FW-140	1/4
QCF-FW-141	1/4
QCF-FW-516	5/16
QCF-FW-380	3/8
QCF-FW-120	1/2
QCF-FW-580	5/8

■ 表 6

①代号	配套螺杆直径
QCF-BR-140	1/4
QCF-BR-141	1/4
QCF-BR-516	5/16
QCF-BR-380	3/8
QCF-BR-120	1/2
QCF-BR-580	5/8

F4  
气快速  
夹钳