

# 全铜快插系列 直角螺纹接头

大批量  
订购   
bulk order

■直角螺纹接头


NEW  
新产品



CAD  
2D/3D

|               |           |              |
|---------------|-----------|--------------|
| ① 代号<br>HGCLR | ② 材质<br>铜 | ③ 表面处理<br>镀镍 |
|---------------|-----------|--------------|

L2  
气动接头



订购编号示例

① 代号 - ② 尺寸系列  
HGCLR - 0602A

| ① 代号  | ② 尺寸系列 | D <sub>2</sub> | T    | L <sub>1</sub> | L <sub>2</sub> | H   | S  | D <sub>1</sub> |
|-------|--------|----------------|------|----------------|----------------|-----|----|----------------|
| HGCLR | 0401A  | φ4             | G1/8 | 17.5           | 15             | 5   | 12 | φ8             |
|       | 0402A  |                | G1/4 | 17.5           | 17             | 7   | 16 |                |
|       | 0403A  |                | G3/8 | 17.5           | 17.5           | 7.5 | 19 |                |
|       | 0601A  | φ6             | G1/8 | 23             | 18.5           | 5   | 12 | φ12            |
|       | 0602A  |                | G1/4 | 23             | 20.5           | 7   | 16 |                |
|       | 0603A  |                | G3/8 | 23             | 21             | 7.5 | 19 |                |
|       | 0604A  |                | G1/2 | 23             | 23             | 9   | 24 |                |
|       | 0801A  | φ8             | G1/8 | 25             | 19             | 5   | 13 | φ14            |
|       | 0802A  |                | G1/4 | 25             | 21             | 7   | 16 |                |
|       | 0803A  |                | G3/8 | 25             | 21.5           | 7.5 | 19 |                |
|       | 0804A  |                | G1/2 | 25             | 23.5           | 9   | 24 |                |
|       | 1001A  | φ10            | G1/8 | 29.5           | 23             | 5   | 14 | φ16            |
|       | 1002A  |                | G1/4 | 29.5           | 25             | 7   | 16 |                |
|       | 1003A  |                | G3/8 | 29.5           | 25.5           | 7.5 | 19 |                |
|       | 1004A  |                | G1/2 | 29.5           | 27.5           | 9   | 24 |                |
|       | 1201A  | φ12            | G1/8 | 31.5           | 25.5           | 5   | 19 | φ18            |
|       | 1202A  |                | G1/4 | 31.5           | 27.5           | 7   | 19 |                |
|       | 1203A  |                | G3/8 | 31.5           | 28             | 7.5 | 19 |                |
|       | 1204A  |                | G1/2 | 31.5           | 30             | 9   | 24 |                |
|       | 1402A  | φ14            | G1/4 | 35             | 32.5           | 7   | 21 | φ21            |
|       | 1403A  |                | G3/8 | 35             | 33             | 7.5 | 21 |                |
|       | 1404A  |                | G1/2 | 35             | 35             | 9   | 24 |                |
|       | 1602A  | φ16            | G1/4 | 35             | 32.5           | 7   | 21 | φ23            |
|       | 1603A  |                | G3/8 | 35             | 33             | 7.5 | 21 |                |
| 1604A | G1/2   |                | 35   | 35             | 9              | 24  |    |                |
| 1606A | G3/4   |                | 35   | 38             | 12             | 30  |    |                |