



Aufnahmebolzen



Form A

l	h 1	h 2	$\varnothing d_2$ mm	$\varnothing d_1$ mm	L mm	VPE	Art.-Nr.
6	7	4	4	6	13	4 / 10 / 30	8228-K-72880
6	12	4	4	6	18	4 / 10 / 30	8228-K-72881
9	10	6	6	8	19	4 / 10 / 30	8228-K-72882
9	16	6	6	8	25	4 / 10 / 30	8228-K-72883
9	10	6	6	10	19	4 / 10 / 30	8228-K-72884
9	18	6	6	10	27	4 / 10 / 30	8228-K-72885
9	10	6	6	12	19	4 / 10 / 30	8228-K-72886
9	18	6	6	12	27	4 / 10 / 30	8228-K-72887
12	13	8	8	16	25	4 / 10 / 30	8228-K-72888
12	22	8	8	16	34	4 / 10 / 30	8228-K-72889




Form C

l	h 1	h 2	$\varnothing d_2$ mm	$\varnothing d_1$ mm	s	L mm	SW	VPE	Art.-Nr.
6	7	4	4	6	1	13	3,8	4 / 10 / 30	8228-K-72896
6	12	4	4	6	1	18	3,8	4 / 10 / 30	8228-K-72897
9	10	6	6	8	1,6	19	5,3	4 / 10 / 30	8228-K-72898
9	16	6	6	8	1,6	25	5,3	4 / 10 / 30	8228-K-72899
9	10	6	6	10	2,5	19	7	4 / 10 / 30	8228-K-72900
9	18	6	6	10	2,5	27	7	4 / 10 / 30	8228-K-72901
9	10	6	6	12	2,5	19	8	4 / 10 / 30	8228-K-72902
9	18	6	6	12	2,5	27	8	4 / 10 / 30	8228-K-72903
12	13	8	8	16	3,5	25	10,8	4 / 10 / 30	8228-K-72904
12	22	8	8	16	3,5	34	10,8	4 / 10 / 30	8228-K-72905

Form B



l	h 1	h 2	$\varnothing d_2$ mm	$\varnothing d_1$ mm	L mm	VPE	Art.-Nr.
6	7	3	4	3	13	4 / 10 / 30	8228-K-72890
6	12	3	4	3	18	4 / 10 / 30	8228-K-72891
9	10	4	6	4	19	4 / 10 / 30	8228-K-72892
9	16	4	6	4	25	4 / 10 / 30	8228-K-72893
9	10	5	8	6	19	4 / 10 / 30	8228-K-72894
9	18	5	8	6	27	4 / 10 / 30	8228-K-72895



Form D

l	h 1	h 2	$\varnothing d_2$ mm	$\varnothing d_1$ mm	s	L mm	SW	VPE	Art.-Nr.
6	7	3	4	3	1,2	13	2,4	4 / 10 / 30	8228-K-72906
6	12	3	4	3	1,2	18	2,4	4 / 10 / 30	8228-K-72907
9	10	4	6	4	1,6	19	3,2	4 / 10 / 30	8228-K-72908
9	16	4	6	4	1,6	25	3,2	4 / 10 / 30	8228-K-72909
9	10	5	8	6	2	19	4,5	4 / 10 / 30	8228-K-72910
9	18	5	8	6	2	27	4,5	4 / 10 / 30	8228-K-72911

Anwendungsbeispiel



Anwendungsbeispiel

