




COLONNA DI GUIDA A DUE DIAMETRI
GUIDE PILLAR WITHOUT CENTERING COLLAR
FÜHRUNGSSÄULE OHNE ZENTRIERBUND

ECO-1

Acciaio: Da cementazione
Steel: Case hardened
Stahl: Einsatzhärtung

Durezza: HRC 60-62
Hardness: HRC 60-62
Härte: HRC 60-62



D1	D2	D3	K	L2	L1	L																	
						50	60	70	80	90	100	120	140	160	180	200	220	240	260	280	300	340	
12	18	22	5	5	22	-	-	-	-														
					26	-	-	-	-														
					36	-	-	-	-	-	-												
					46	-	-	-	-	-	-												
14	20	24	5	5	22	-	-	-	-	-													
					26	-	-	-	-	-	-												
					36	-	-	-	-	-	-												
					46	-	-	-	-	-	-												
16	22	26	5	5	22	-	-	-	-														
					26	-	-	-	-	-	-												
					36	-	-	-	-	-	-												
					46	-	-	-	-	-	-	-											
					56	-	-	-	-	-	-	-	-										
					66	-	-	-	-	-	-	-	-	-									
18	26	30	5	5,5	26	-	-	-	-	-													
					36	-	-	-	-	-	-												
					46	-	-	-	-	-	-	-											
					56	-	-	-	-	-	-	-	-										
					66	-	-	-	-	-	-	-	-	-									
					76	-	-	-	-	-	-	-	-	-	-								
20	28	32	6	6	26	-	-	-	-	-	-												
					36	-	-	-	-	-	-	-											
					46	-	-	-	-	-	-	-	-										
					56	-	-	-	-	-	-	-	-	-									
					66	-	-	-	-	-	-	-	-	-	-								
					76	-	-	-	-	-	-	-	-	-	-	-							
					86	-	-	-	-	-	-	-	-	-	-	-	-						
96	-	-	-	-	-	-	-	-	-	-	-	-	-										

Esempio di ordinativo: D1xL1xL **Order example:** D1xL1xL **Bestellbeispiel:** D1xL1xL

*da specificare - *to specify - *muss angegeben werden




COLONNA DI GUIDA A DUE DIAMETRI
GUIDE PILLAR WITHOUT CENTERING COLLAR
 FÜHRUNGSSÄULE OHNE ZENTRIERBUND

ECO-1

Acciaio: Da cementazione
Steel: Case hardened
Stahl: Einsatzhärtung

Durezza: HRC 60-62
Hardness: HRC 60-62
Härte: HRC 60-62



D1	D2	D3	K	L2	L1	L																												
						50	60	70	80	90	100	120	140	160	180	200	220	240	260	280	300	340	400											
25	34	38	7	7	26																													
					36																													
	36*	40																																
	46																																	
	56																																	
	66																																	
32	40	45	7	7,5	36																													
					46																													
					56																													
					66																													
					76																													
					86																													
40	48	52	8	8	46																													
					56																													
					66																													
					76																													
					86																													
					96																													
50	60	65	10	9	96																													
					126																													
					146																													
					176																													

Esempio di ordinativo: D1xL1xL **Order example:** D1xL1xL **Bestellbeispiel:** D1xL1xL

*da specificare - *to specify - *muss angegeben werden