




Busbar systems Flat-PLS

System components

Connection system		Flat-PLS 60		Flat-PLS 100								
		Model No. SV		Model No. SV								
	A Angular connector for Flat-PLS For connecting horizontal Flat-PLS busbar systems in the roof/base section and vertical Flat-PLS busbar systems.											
	Bar population up to mm	For enclosure depth mm	No. of brackets mm	Packs of								
	2 x 40 x 10	600/800	2 x 40 x 10	1	9675.842	–						
	2 x 60 x 10	600/800	3 x 40 x 10	1	9675.843	–						
	4 x 60 x 10	600/800	3 x 80 x 10	1	9675.883	–						
	4 x 40 x 10 mm or 2 x 100 x 10	600/800	2 x 80 x 10	1	9675.882	9675.882						
	4 x 80 x 10	600/800	2 x 100 x 10	1	–	9675.892						
4 x 100 x 10	600/800	3 x 100 x 10	1	–	9675.893							
Also required												
Claw with threaded insert			see page 335									
Screw connections			see page 335									
Contact makers			see page 334									
	B Angular connector for Flat-PLS For connecting horizontal Flat-PLS busbar systems in the rear section to vertical Flat-PLS busbar systems.											
	Bar population up to mm	For conductor	For enclosure depth mm	Angular version mm	Packs of							
	2 x 60 x 10	L1, L2, L3	600	3 x 40 x 10	1 set	9675.846	–					
		N		3 x 40 x 10	1 set	9675.847	–					
	4 x 60 x 10	L1, L2, L3		3 x 80 x 10	1 set	9675.886	–					
		N		3 x 80 x 10	1 set	9675.887	–					
	2 x 60 x 10	L1, L2, L3		800	3 x 40 x 10	1 set	9675.848	–				
		N			3 x 40 x 10	1 set	9675.849	–				
	4 x 60 x 10	L1, L2, L3	3 x 80 x 10		1 set	9675.888	–					
		N	3 x 80 x 10		1 set	9675.889	–					
	2 x 100 x 10	L1, L2, L3	600		2 x 80 x 10	1 set	–	9675.876				
	4 x 100 x 10	L1, L2, L3			3 x 100 x 10	1 set	–	9675.896				
	2 x 100 x 10	L1, L2, L3		800	2 x 80 x 10	1 set	–	9675.878				
		N			2 x 80 x 10	1 set	–	9675.877				
	4 x 100 x 10	L1, L2, L3			3 x 100 x 10	1 set	–	9675.898				
N		3 x 100 x 10			1 set	–	9675.897					
	C T-connector kits for Flat-PLS/RiLine60 bar systems. For connecting horizontal Flat-PLS main busbar systems to vertical RiLine60 distribution busbar systems in the modular outgoing section. Sets of screws for connection to distributor busbar system.											
	Flat-PLS		Distribution busbar system				Enclosure depth mm	Packs of	3-pole	4-pole	3-pole	4-pole
	In the roof/base section	In the rear section top/bottom	Behind the compartment	Inside the compartment	600	800						
		30 x 10/5 mm	PLS 1600	30 x 10/5 mm	PLS 1600							
■	–	■	–	–	–	■	–	1 set	9675.501	9675.502	9675.511	–
■	–	■	–	–	–	–	■	1 set	9675.503	9675.504	9675.513	9675.514
■	–	–	■	–	–	■	–	1 set	9675.505	9675.508	9675.515	–
■	–	–	■	–	–	–	■	1 set	9675.506	9675.507	9675.516	9675.517
■	–	–	–	■	–	■	–	1 set	9675.521	9675.522	9675.531	–
■	–	–	–	■	–	–	■	1 set	9675.523	9675.524	9675.533	9675.534
■	–	–	–	–	■	■	–	1 set	9675.525	9675.528	9675.535	–
■	–	–	–	–	■	–	■	1 set	9675.526	9675.527	9675.536	9675.537
–	■	■	–	–	–	–	■	1 set	9675.543	9675.544	9675.553	9675.554
–	■	–	■	–	–	–	■	1 set	9675.546	9675.547	9675.556	9675.557
–	■	–	–	■	–	–	■	1 set	9675.563	9675.564	9675.573	9675.574
–	■	–	–	–	■	–	■	1 set	9675.566	9675.567	9675.576	9675.577
Also required												
Spacer rolls						see page 353						
Screw connections						see page 335						
Claw with threaded insert						see page 335						