



Adaptor nipple



Draadeind
Gewindestück
Embout fileté
Manicotto nipplo
Manchon de transición



Art.code	d1	d2	d3	Z	B	C	D	PN	Quantity
3.20.030	25	32	1/2" (M)	6	22	19	18	10	500
3.20.045	25	32	3/4" (M)	6	22	19	17	10	500
3.20.050	25	32	1" (M)	5	22	19	18	10	500
3.20.055	32	40	1" (M)	5	23	22	17	10	500
3.20.060	32	40	1 1/4" (M)	4	23	22	18	10	600
3.20.065	40	50	1 1/4" (M)	11	31	26	23	10	300
3.20.070	40	50	1 1/2" (M)	12	31	26	23	10	275
3.20.075	50	-	1 1/2" (M)	12	-	31	23	10	200
3.20.080	50	-	2" (M)	12	-	31	27	10	150
3.20.090	63	-	2" (M)	8	-	38	27	10	100

Adaptor nipple

Inzetdraadeind
Gewindestück
Embout fileté
Nipplo
Nipple de transición



Art.code	d1	d2	d3	Z	B	C	D	S	PN	Quantity
3.30.010	-	16	1/4" (M)	8	14	-	27	13	16	100
3.30.011	-	16	3/8" (M)	8	14	-	27	15	16	100
3.30.012	-	16	1/2" (M)	8	14	-	27	19	16	100
3.30.015	-	20	3/8" (M)	8	16	-	32	15	16	100
3.30.016	-	20	1/2" (M)	8	16	-	32	19	16	100
3.30.017	-	20	3/4" (M)	8	16	-	32	19	16	100
3.30.020	-	25	1/2" (M)	9	19	-	36	19	16	100
3.30.025	-	25	3/4" (M)	9	19	-	36	19	16	100
3.30.030	-	25	1" (M)	9	19	-	36	21	16	100
3.30.040	25	32	3/4" (M)	10	22	19	46	19	16	100
3.30.045	25	32	1" (M)	10	22	19	46	21	16	100
3.30.046	25	32	1 1/4" (M)	10	22	19	46	23	16	100
3.30.050	-	40	1" (M)	11	26	-	55	21	16	100
3.30.055	-	40	1 1/4" (M)	11	26	-	55	23	16	100
3.30.060	-	50	1 1/4" (M)	12	31	-	65	23	16	100
3.30.065	-	50	1 1/2" (M)	12	31	-	65	23	16	100
3.30.070	-	63	1 1/4" (M)	13	38	-	80	23	16	100
3.30.075	-	63	1 1/2" (M)	13	38	-	80	23	16	100
3.30.080	-	63	2" (M)	13	38	-	80	27	16	100