


UITVOERING C1 / BAUFORM C1 / MOUNTING STYLE C1



TYPE CILINDER	Afmetingen (mm)															
	R	L3	L4	A	E	G	H	J	K	N1	c1	d1	l	m2	x2	y1
ACDC1- 25/ 12	R1/8"	72	21	35	M10 x 1,5	85	68	50	26	9	3	10	38	40	8	15
ACDC1- 25/ 16	R1/8"	70	26	35	M10 x 1,5	85	68	50	26	9	3	10	25	55	10	15
ACDC1- 30/ 20 22	R1/4"	108	25	40	M14 X 1,5	94	75	60	36	9	5	12	53	60	10	14
ACDC1- 32/ 20 22	R1/4"	108	25	42	M14 X 1,5	94	75	60	37	9	5	12	53	60	10	14
ACDC1- 35/ 20 22 25	R1/4"	108	25	45	M14 x 1,5	94	75	60	39	9	5	12	53	60	10	14
ACDC1- 40/ 20 22 25 28 30	R3/8"	119	27	50	M16 x 1,5	104	85	65	41	11	5	15	48	67	12	16
ACDC1- 50/ 25 30 35	R3/8"	135	30	60	M16 x 1,5	118	95	75	46	11	5	18	57	75	15	16
ACDC1- 60/ 30 35 40	R1/2"	148	31	70	M22 x 1,5	138	115	90	53	13	5	22	61	82	16	22
ACDC1- 63/ 32 35 36 40 45	R1/2"	148	31	75	M22 x 1,5	138	115	90	56	13	5	22	61	82	16	22
ACDC1- 65/ 30 32 35 40 45	R1/2"	148	31	75	M22 x 1,5	138	115	90	56	13	5	22	61	82	16	22
ACDC1- 70/ 35 40 45 50	R1/2"	148	31	80	M22 x 1,5	138	115	90	58	13	5	22	61	82	16	22
ACDC1- 80/ 40 45 50 55 60	R1/2"	167	32	95	M28 x 1,5	178	145	115	66	17	5	25	68	93	17	28
ACDC1- 90/ 45 50 55 60 65	R1/2"	167	32	105	M28 x 1,5	178	145	115	71	17	5	25	68	93	17	28
ACDC1-100/ 50 55 60 70	R1/2"	175	32	115	M35 x 1,5	205	170	140	76	17	5	35	64	101	17	35
ACDC1-110/ 50 55 60 70	R1/2"	175	32	130	M35 x 1,5	205	170	140	84	17	5	35	64	101	17	35
ACDC1-120/ 60 70 80 85	R3/4"	208	42	140	M45 x 1,5	245	205	165	91	21	5	40	73	128	25	45
ACDC1-125/ 60 70 80 85 90	R3/4"	208	42	145	M45 x 1,5	245	205	165	94	21	5	40	73	128	25	45
ACDC1-130/ 70 80 85	R3/4"	208	42	150	M58 x 1,5	245	205	165	96	21	5	40	73	128	25	58
ACDC1-140/ 70 80 85 90 100	R3/4"	265	52	160	M65 x 1,5	280	240	203	101	21	5	45	108	147	35	65
ACDC1-150/ 80 85 90 100	R3/4"	265	52	170	M65 x 1,5	280	240	203	106	21	5	45	108	147	35	65
ACDC1-160/ 85 90 100 100	R1"	320	62	180	M80 x 2	335	275	227	115	30	10	55	140	177	37	80
ACDC1-180/ 90 100 110 125 140	R1"	355	67	210	M100 x 2	360	300	253	130	30	10	60	150	207	42	100
ACDC1-200/ 100 110 125 140	R1"	395	82	230	M110 x 2	420	345	288	139	33	10	70	170	237	47	110