




①代号	类型	M材质	S表面处理	最高工作温度
MTU	标准型	钕磁铁	镀镍	80° C
MTX		耐热钕磁铁		150° C
MTY		强力钕磁铁		60° C
MTV		钴磁铁		200° C



①代号 - ②D - ③T
 MTU - D2 - T3

①代号	②D	③T	吸附力(kgf)		表面磁通密度高斯(G)	
			MTU·MTX·MTY	MTV	MTU·MTX·MTY	MTV
1		2	0.006	0.004	1200~1600	700~1100
		3	0.007	0.005	1200~1600	800~1200
		5	0.008	0.006	1200~1600	900~1300
		2	0.06	0.04	2400~2800	1800~2200
		3	0.07	0.05	2400~3000	2400~2800
2		4	0.07	-	2800~3000	-
		5	0.08	0.05	2800~3200	2400~2800
		1	0.11	-	2000~2500	-
		2	0.16	0.11	2900~3300	2400~2800
		3	0.2	0.14	3400~3900	2600~3000
3		4	0.23	0.15	3600~3900	2700~3100
		5	0.24	0.16	3800~4200	2700~3100
		6	0.29	-	4100~4300	-
		1	0.15	-	1900~2300	-
		2	0.29	0.19	3000~3400	2400~2800
4		3	0.39	0.26	3500~3900	2900~3300
		4	0.44	0.3	3800~4300	3000~3400
		5	0.48	0.32	4000~4400	3200~3600
		8	0.69	-	4500~4700	-
		10	0.72	-	4500~4700	-
5		1	0.16	-	1600~1900	-
		2	0.4	0.27	2900~3300	2700~2700
		3	0.59	0.39	3500~4000	3000~3400
		4	0.7	0.47	4000~4300	3200~3600
		5	0.78	0.52	4100~4600	3400~3800
(钕磁铁) MTU (耐热钕磁铁) MTX (强力钕磁铁) MTY (钴磁铁) MTV		6	0.83	0.55	4200~4600	3400~3800
		8	0.92	-	4700~4900	-
		10	1	-	4400~4900	-
		2	0.51	0.34	2600~3000	2200~2600
		3	0.78	0.52	3500~3800	2900~3300
6		4	0.98	0.66	3700~4100	3100~3500
		5	1.11	0.74	4100~4600	3400~3800
		6	1.2	0.8	4300~4800	3500~3900
		8	1.28	-	4600~4900	-
		10	1.3	-	4600~5100	-
8		2	0.68	0.45	2500~2800	1800~2200
		3	1.1	0.76	3300~3600	2500~2900
		5	1.83	1.22	4100~4500	3300~3700
		6	2.1	-	4500~4900	-
		8	2.35	1.57	4500~4900	3700~4100
10		10	2.45	-	4800~5100	-
		2	0.8	0.54	2400~2700	1500~1900
		3	1.44	0.96	2700~3100	2200~2600
		5	2.53	1.69	3900~4400	3000~3400
		8	3.5	2.35	4600~4900	3800~4200
12		10	3.88	2.6	4800~5100	3900~4300
		2	0.92	0.61	2200~2600	1100~1500
		3	1.68	1.13	2600~2600	1900~2300
		5	3.18	2.13	3500~3800	2800~3200
		8	4.75	3.17	4300~4600	3600~4000
15		10	5.38	3.6	4600~4900	3800~4200
		2	1.08	0.72	2200~2500	900~1300
		3	2	1.34	2800~3200	1700~2100
		5	4.04	2.7	3600~3900	2400~2800
		8	6.57	4.39	4200~4700	3300~3700
20		10	7.74	5.17	4600~4900	3600~4000
		3	3.5	-	2400~2800	-
		10	10	-	4200~4500	-

▲ 吸附力、表面磁通密度为参考值。