





# 拆卸式合页



①代号	类型	拔插方向	④材质	⑤表面处理
HGCIZA	拔插型	左右偏置锥孔型	钛合金	抛丸处理
HGCIZB		左侧		
HGCIZC	锥孔型	右侧		
HGCIZD		左侧		
		右侧		



▲ 图为左侧插拔型。



视角标准：第一视角



①代号 - ②规格  
HGCIZA - 65

型号		L	H	L <sub>1</sub>	L <sub>2</sub>	H <sub>1</sub>	H <sub>2</sub>	H <sub>3</sub>	H <sub>4</sub>	T	d <sub>1</sub>	d <sub>2</sub>	F	N	M	参考重量 (kg/pcs)
①代号 HGCIZA HGCIZB	②规格 65	50	65	36	30	10.5	22	-	22	2.5	5	10.5	26	6	M4	0.07
	75	70	75	50	40	27	27	27	3	6	12	29	6	M5		
	100	82	100	60	40	11	26	26	26	4	8	16	39	8		

型号		L	H	L <sub>1</sub>	H <sub>1</sub>	F	d <sub>1</sub>	d <sub>2</sub>	T	负载 (kg)	参考重量 (kg/pcs)
①代号 HGCIZC HGCIZD	②规格 50	32	50	21	20	24				7	0.02
	64	36	64	24	24	31	4	7.3	1.5	10	
	75	38	75	24	30	35		8.3	2	15	



数量分类	小单	中大单	大单
数量	1~50	51~100	100~
交货期	通常	7工作日	现询



数量	1-9	10~
价格	100%	现询

G1  
手柄  
合页  
门组件  
手轮  
拉手

