





★ 产品特点：可通过固定型，结合板的宽度进行高精度定位。

类型		M材质	H硬度
PCCHE	标准型	相当于 S45C	42 ~ 45HRC
PCCHH			
PCCHF	螺纹孔型		
PCCHG	加长型		




按图定制




标准型      螺纹孔型


  



加长型



组装尺寸



视角标准：第一视角



①代号 - ②T  
PCCHE - T12

①代号	②T	L	L <sub>1</sub>	L <sub>2</sub>	A	H	d	R	M	
									(粗牙螺纹)	
标准型	PCCHE	12		25	26	20	9.5	5.5	2	
		16	35	27	28	25	14	9	4	
		19								
	PCCHH	12		19	22	20	9.5	5.5	2	-
		16	25	21	24	25	11	7	4	
		19								
螺纹孔型	PCCHF	16	25	21	24	25	11	7	4	M6
加长型	PCCHG	12		25	26	20	9.5	5.5	2	
		16	35	27	28	25	14	9	4	-
		19								



交货期 3天发货



数量分类	标准订单	特殊订单
	数量	小单 1~100
交货期	3天发货	另报价

▲常州·东莞发货。  
▲部分产品7天发货，请以实际报价为准。

