


标准型

# 推拉压紧式气动夹钳





视角标准：第一视角

★ 产品特点：主体材质Q235，行程23.6



① 代号  
QC3-305-EA

① 代号	底座样式	夹持力 (kg)	压头螺丝	气缸直径	气缸受压面积 (cm <sup>2</sup> )	自重 (g)	最大气压 (kg/cm <sup>2</sup> )(PSI)	主体材质
QC3-305-EA	法兰底座	386	QS-SA-105015	32	12.56	1540	10(140)	碳钢



视角标准：第一视角

★ 产品特点：主体材质Q235，行程19.7



① 代号  
QC3-36003-A

① 代号	底座样式	夹持力 (kg)	压头螺丝	气缸直径	气缸受压面积 (cm <sup>2</sup> )	自重 (g)	最大气压 (kg/cm <sup>2</sup> )(PSI)	主体材质
QC3-36003-A	法兰底座	272	QC-SA-085012	32	7.07	960	10(140)	碳钢



百万商品齐上线，获取专属企业折扣，轻松下单



400-6699-428



www.ant-fa.com

F3  
气快速  
夹钳