


内六角螺栓

圆柱头型




■ 圆柱头型



① 代号	类型	[M] 材质	[S] 表面处理	强度等级	
SWLAA	标准型	全牙 / 半牙	ML40Cr	发黑	12.9
SWLBA			SUS304	-	A2-70
SWLDA		全牙	一般结构钢	镀锌	8.8
SWLEA			SUS316	-	A4-70

产品特点：用于施加较大拧紧力矩、链接强度高、头部能埋在零件内、结构要求紧凑、外形平滑的链接场合。如刨床、导轨等处。

▲ 适用标准：GB/T70.1-12000
▲ 相当 DIN912-1983



订购编号示例

① 代号	-	② M	-	③ L
SWLAA	-	M5	-	L10

① 代号	② M	③ L	主要尺寸						
			螺距 P	B	D	H	S	W	
SWLAA SWLBA SWLDA SWLEA	2	3	0.4	全牙	3.8	2	1.5	1	
		4							
		5							
		6							
		8							
		10							
		12							
		14							
	2.5	4	0.45	全牙	4.5	2.5	2	1.1	
		5							
		6							
		8							
		10							
		12							
		16							
		18							
3	5	0.5	全牙	5.5	3	2.5	1.3		
	6								
	8								
	10								
	12								
	14								
	16								
	18								
4	5	0.7	全牙	7	4	3	2		
	6								
	8								
	10								
	12								
	14								
	20		16	20	全牙	7	4	3	2
			18						
			20						
			22						
			25						
			30						

① 代号	② M	③ L	主要尺寸												
			螺距 P	B	D	H	S	W							
SWLAA SWLBA SWLDA SWLEA	5	6	0.8	全牙	8.5	5	4	2.5							
		8													
		10													
		12													
		14													
		16													
		18													
		20													
	6	22	1	全牙	10	6	5	3							
		25													
		30													
		35													
		40													
		24													
		8							8	1.25	全牙	13	8	6	4
									10						
12															
14															
16															
18															
10	20		1.5	全牙	16	10	8	5							
	22														
	25														
	30														
	35														
	40														
	28	40							32	全牙	16	10	8	5	
		45													
		50													
		55													
		60													

F6
垫片 / 螺母