

六角头螺栓

六角头螺栓全螺纹 / 六角法兰面螺栓



■六角头螺栓全螺纹




① 代号	类型	螺纹	[M] 材质	[H] 硬度	[S] 表面处理	强度等级
SWWAE	全牙	粗牙	SCM435	32~39HRC	发黑	8.8
SWWDE			一般结构钢	—	镀锌	8.8
SWWBE			SUS304	—	—	A2-70

产品特点: 不锈钢材质, 耐腐蚀耐酸, 不易老化, 内六角设计, 锁紧更省力。

△适用标准: GB/T 5783-2016

订购编号示例

① 代号	-	② M	-	③ L
SWWAE	-	M5	-	L10



① 代号	② M	③ L																		P 螺距	S	K													
SWWAE SWWDE	5	8	10	12	14	16	18	20	25	30	35	40	45													0.8	8	3.5							
	6	10	12	14	16	18	20	25	30	35	40	45	50	55	60	65	70	75													1	10	4		
	8	12	14	16	18	20	25	30	35	40	45	50	55	60	65	70	75	80	90	100													1.25	13	5.3
	10	16	18	20	25	30	35	40	45	50	55	60	65	70	75	80	90	100													1.5	17	6.4		
	12	20	25	30	35	40	45	50	55	60	65	70	75	80	90	100	110	120	130													1.75	19	7.5	
	16	30	35	40	45	50	55	60	65	70	75	80	90	100	110	120	130													2	24	10			
20	60	90	100	110	120	130	140	150	160	180	190	200	220	350													2.5	30	12.5						