

圆形截面圆柱形拉伸弹簧

轻载型

■轻载型




① 代号		类型	④ 材质
ESBJP	平行向		轻载型
ESBJC	垂直向	SUS304-WPB	
ESBHC	平行向		
ESBHC	垂直向		


J2
弹
簧

订购编号示例

① 代号	-	② D	-	③ L
ESBJP	-	D2	-	L10



ESBJP
ESBHP
平行向



ESBJC
ESBHC
垂直向

① 代号	② D	③ L	d	动态负载时		(初拉力) (N)	弹簧系数 (N/mm)
				工作行程 S (mm)	工作极限载荷 (N)		
ESBJP ESBHP	2	10	0.25	5.70	1.86	0.34	0.27
		15		10.30			0.15
		20		14.00			0.11
		25		18.20			0.08
		30		22.10			0.07
ESBJP ESBHP ESBJC ESBHC (括号内尺寸仅限 ESBJP、ESBHP)	3	10	0.3	8.70	2.25	0.29	0.23
		15		16.60			0.12
		20		25.00			0.08
		25		33.30			0.06
		30		40.00			0.05
	4	15	0.4	10.00	3.24	0.59	0.26
		20		16.80			0.16
		25		22.50			0.12
		30		28.40			0.09
		35		33.70			0.08
	5	20	0.5	6.80	4.22	0.88	0.49
		25		11.70			0.28
		30		17.00			0.20
		35		21.20			0.16
		40		26.10			0.13
6	40	0.6	34.00	8.14	1.27	0.10	
	45		37.70			0.09	
	50		42.50			0.08	
	20		14.00			0.49	
	25		21.20			0.32	
	30		28.00			0.25	
	35		35.00			0.20	
	40		41.10			0.17	
8	45	0.8	50.00	12.75	2.35	0.14	
	50		53.80			0.13	
	55		63.60			0.11	
	60		70.00			0.10	
	25		15.10			0.69	
	30		21.20			0.49	
	35		26.50			0.39	
	40		33.10			0.31	
	45		39.20			0.26	
	55		48.10			0.22	
10	60	1	53.00	15.00	3.73	0.20	
	65		58.80			0.18	
	70		66.20			0.16	
	30		11.50			0.98	
	35		15.30			0.74	

分类
目录



返回
主目录



圆形截面圆柱形拉伸弹簧

轻载型

①代号	② D	③ L	d	动态负载时		(初拉力) (N)	弹簧系数 (N/mm)
				工作行程 S (mm)	工作极限载荷 (N)		
ESBJP ESBHP ESBJC ESBHC (括号内尺寸仅限 ESBJP、ESBHP)	10	40	1	19.80	15.00	3.73	0.57
		45		23.90			0.47
		50		28.70			0.39
		55		32.80			0.34
		60		37.00			0.30
		65		39.60			0.29
		70		44.20			0.26
		75		47.90			0.24
		80		52.20			0.22
		(90)		60.50			0.19
	(100)	71.80	0.16				
	12	1.2	35	22.00	31.37	5.39	1.18
			40	27.80			0.93
			45	35.30			0.74
			50	42.00			0.62
			55	50.00			0.52
			60	55.20			0.47
			65	63.00			0.41
			70	69.70			0.37
			75	77.90			0.33
80			82.80	0.31			
90	91.30	0.29					
100	106.0	0.25					
ESBJP ESBHP	14	40	1.5	15.40	38.24	8.43	1.94
		45		21.00			1.42
		50		25.40			1.17
		55		30.80			0.97
		60		37.00			0.80
		65		43.20			0.69
		70		46.20			0.64
		75		52.80			0.56
		80		58.30			0.51
		90		68.10			0.43
	100	76.40	0.39				
	125	91.00	0.33				
	16	1.6 (仅限 SWP-A) 1.7 (仅限 SUS304- SWPB)	45	15.80	43.15	9.12	2.16
			50	21.00			1.62
			55	25.70			1.32
			60	31.50			1.08
			65	35.80			0.95
			70	40.80			0.83
			75	46.30			0.74
			80	49.60			0.69
90			60.90	0.56			
100			69.40	0.49			
125	91.30	0.37					
150	115.6	0.29					
ESBJP	18	50	1.8	21.00	52.96	9.81	2.05
		55		26.00			1.66
		60		31.00			1.39
		65		36.00			1.20
		70		42.00			1.03
		75		46.00			0.94
		80		54.00			0.80
		90		66.00			0.65
		100		75.00			0.58
		125		104.5			0.41
	150	132.0	0.33				
	20	2	60	29.10	78.45	12.75	2.26
			70	41.80			1.57
			80	53.60			1.23
			90	67.00			0.98
			100	78.80			0.83
			125	111.6			0.59
			150	139.5			0.47
			175	167.5			0.39

▲初拉力、弹簧系数为参考值。载荷 (kgf) = 载荷 N × 0.101972

J2
弹
簧

分类
目录
返回
主目录