



螺纹式弹簧柱塞



F4
弹簧柱塞



①代号	类型	主体		前端		弹簧	可使用温度
		M材质	H硬度	M材质	H硬度		
PHMUA PHMUB PHMUF PHMUG	不锈钢 主体型	相当于 SUS304	SUS440C	55HRC~	SUS631	-30~260°C	
PHMVA PHMVB PHMVF PHMVG			聚缩醛	-			-30~80°C



①代号 - ②M - ③E
PHMUA - M5 - E5

①代号	②M (粗牙螺纹)	③E	d	L ₁	L	S	超轻型(PHMVA、PHMUA)		轻型(PHMUB、PHMVB)		重型(PHMUF、PHMVF)		超重型(PHMUG、PHMVG)	
							许用载荷(N)		许用载荷(N)		许用载荷(N)		许用载荷(N)	
							min.	max.	min.	max.	min.	max.	min.	max.
金属球头 PHMUA PHMUB PHMUF PHMUG	3	1.5	1	15	15	0.9	0.12	0.4	0.4	1.3	0.8	2.94	1.1	3.42
		3		15	15		0.12	0.4	0.2	1.3	0.6	2.93	0.8	3.41
	4	2	1.6	15	15	1.3	0.27	0.65	0.9	2	2	8.8	6.1	13.8
		4		24	24		0.18	0.65	0.6	2.1	1.9	8.75	5.8	13.6
	5	3	2	20	20	1.5	0.4	3	1.4	9.7	2.7	16.3	6.8	22
		5		27	27		0.35	3	1.1	10.3	1	17.1	5.7	21.5
6	3	2.5	25	25	2	1.8	3.05	6	9.8	8	26.4	15.8	35.6	
	5		30	30		1.5	3.05	3.4	9.86	4.4	26.6	12.9	34.4	
树脂球头 PHMVA PHMVB PHMVF PHMVG	8	3	3.1	25	25	2.5	1.9	3.15	6	9.9	14.7	27	21.9	36.3
		5		27	27		1.4	3.15	4	9.83	6.7	26.6	14.7	34.5
10	5	3.8	30	30	3	1.6	4.6	5.7	14.7	8.2	45.7	24.5	58.6	
	10		30	43		1.6	4.6	4.4	14.7	6.2	45.1	19.8	58.7	
12	5	5.5	30	30	4	1.7	4.7	5.8	14.7	18.2	49	34.9	63.6	
	10		35	43		1.6	4.7	5	14.7	8.2	49.1	25.5	63.6	
16	15	8	35	51	5	1.8	4.7	6.9	14.7	7.5	48.9	20.1	63.7	
	10		35	57		2.8	10.8	9.2	34.2	18.9	68.5	38.7	88.4	
20	15	8	35	57	5	2.6	10.8	8.6	34.4	14.4	68.6	33.9	88.1	
	20		35	65		2	11	7.1	34.4	4.2	68.6	25.4	88.1	

▲ 拆装时,请勿使用后方的内六角孔。
 ▲ min.表示弹簧柱塞接触时,稍尚未压缩时的力量。
 ▲ max.表示弹簧柱塞的销压缩到终点的力量。

