



国产拖链/接头/分隔片




代码	类型	打开方式	横梁	材质	颜色	允许温度	阻燃等级	附件
DGT20L	20系列拖链	内外径打开	桥式	增强尼龙6	黑色	-20°C~80°C	UL94-HB	接头
DGU20L			全封闭式					



H=理论安装高度
Hf=实际安装高度
D=拖链返回极限位置时的最小距离
K=π*R+安全量



架空长度 FLx: 直线架空长度
FLz: 安全塌腰架空长度



▲ 每米链节数22

M1
拖链



①代号 - ②内宽B₁ - ③弯曲半径R - ④链节数N
DGT20L - 38 - R75 - N20

①代号	②内宽B ₁	③弯曲半径R	④链节数N	接头	安装尺寸			实际安装高度H _f	外宽B ₂	节距P	最大电缆直径(mm)	最大架空负载(kg/m)	最大允许行程(m)	最大垂直悬挂(m)	重量 kg/m	
					H	D	K								DGT20L	DGU20L
DGT20L DGU20L		(40)	1~	D20FJ-25	115	104	230	150	41	46	17	1	60.0	25	-	-
		55			145	119	330	180								
		(25) 75			185	139	368	220								
		100			235	164	414	270								
		125			285	189	506	320								
	38	(40)	D20FJ-38	115	104	230	150	54	≈0.82						≈0.92	
		55		145	119	330	180									
		75		185	139	368	220									
		100		235	164	414	270									
	125	285	189	506	320											
	50	(40)	D20FJ-50	115	104	230	150	66	≈0.9						≈1.04	
		55		145	119	330	180									
		75		185	139	368	220									
		100		235	164	414	270									
	125	285	189	506	320											
	57	(40)	D20FJ-57	115	104	230	150	73	-						-	
55		145		119	330	180										
75		185		139	368	220										
100		235		164	414	270										
125		285		189	506	320										