


内径G6外径m6/内径G6外径h6

# 铜合金直柱型/薄壁型



★ 产品特点：衬套和g6公差导向轴配合间隙小，推荐使用只转螺丝固定，可实现高精度直线运动和旋转运动，适用于中低速的场合。



①代号	类型	□材质	内径公差	外径公差	硬度 HB	使用温度范围 (°C)
OFABP	直柱标准型	高力黄铜+ 固体润滑剂GR1	G6	m6	≥210	-50~150
OFABPU	直柱薄壁型					
OFABZP	直柱标准型			h6		

▲ 配套轴(大气、油中使用)公差推荐(仅供参考): g6: 高精度用  
 ▲ 基座孔推荐公差: H7

K部(两端)放大图

视角标准：第一视角



①代号 - ②d - ③L  
OFABP - d10 - L25

①代号	型号	OFABP			OFABPU			OFABZP			③L								
		②d <sub>G6</sub>	D <sub>m6</sub>	R	D <sub>m6</sub>	R	D <sub>h6</sub>	R	8	10	12	15	16	20	25	30	40		
OFABP OFABPU OFABZP	5	+0.012 +0.004	9	+0.015 +0.006	0.5	7	0.3	-	-	0.5	8	10	12	15	16				
	6		10	8		+0.015 +0.006		10	0		-0.009	8	10	12	15	16	20		
	8		12	10		12		0	-0.011		10	12	15	16	20	25			
	10	+0.014 +0.005	14	+0.018 +0.007		12		14			10	12	15	16	20	25	30		
	12	+0.017 +0.006	18	+0.021 +0.008	1	15	+0.018 +0.007	0.4	18	1	10	12	15	16	20	25	30		
	13		19			16	19		0		10	12	15	16	20	25	30		
	15		21			18	21		0		10	12	15	16	20	25	30		
	16	+0.020 +0.007	22	+0.025 +0.009	1.5	20	0.5	0.5	22	1.5	10	12	15	16	20	25	30	40	
	20		28			24			+0.021 +0.008		28		12	15	16	20	25	30	40
	25		33			29			+0.025 +0.009		33	0	-0.016	12	15	16	20	25	30
30		38			34			38			15	16	20	25	30	40			



交货期

5天发货



数量	1-9	10~
折扣率	100%	现询



百万商品齐上线, 获取专属企业折扣, 轻松下单



400-6699-428



www.ant-fa.com