


★ 产品特点：底座由增强尼龙 (PA6) 制成，耐撞击和敲打，耐腐蚀。



①代号	底盘		螺杆	
	②材质	③材质	④表面处理	
SFBCAL	增强尼龙(PA6)	45#	镀铬	
SFSAL		SUS304	无	

SFBCAL  
SFSAL

视角标准：第一视角

①代号 - ②底径 - ③螺纹直径 - ④螺纹长度  
SFBCAL - D50 - M8 - L50

订购编号示例

型号		主要尺寸							承载(kg)	参考重量 (kg/pcs)
①代号	②D	③M	④L	E	E <sub>1</sub>	H	B	F		
钢 SFBCAL 不锈钢 SFSAL	50	M8	50	14	14	28	20	6.5	500	0.08
			100							0.1
		M10	50	17			20	8		0.08
			100							
		M12	50	19			10	0.1		
			100							0.13
	150	0.13								
	60	M10	50	17	32	24	10	1200	0.1	
			100						0.15	
			50	19					0.13	
			100							0.18
			150	0.2						
M14			50	21					14	0.15
		100	0.18							
150		0.2								
M16		50	24	17	34	13	0.18			
		100						0.2		
		150	0.23							
		M10	50	17	14	37	29	8	1200	0.15
	100		0.2							
	M12	50	19	19	39	29	10	0.18		
100		0.23								
150	0.26									
50	0.39									
100	0.45									

⚠ 承载与参考重量仅供参考。

	数量分类		
	小单	中大单	大单
	数量	1~50	51~100
交货期	通常	7工作日	现询

	数量	
	1~9	10~
价格	100%	另行报价

使用示例

