




# 标准型

## ■ 直筒螺帽型



①代号	类型	D 公差	材质				硬度
			花键轴		花键母		
			国标	相当	国标	相当	
BSCN	直筒螺帽型	h7	GCr15	SUJ2	GCr15	SUJ2	高频淬火 58-62HRC

视角标准：第一视角





①代号 - ②D - ③L  
BSCN - D8 - L200



订购编号示例

①代号	花键轴		滚珠列数	C 倒角	花键母					基本额定负载 (kgf)		基本额定扭矩 (kgf·m)		容许静力矩 (kgf·m)		重量				
	②D <sub>h7</sub>	③L 最小单位1			D <sub>1</sub>	L <sub>1</sub>	L <sub>2</sub>	S	Q 油孔	b	t	C	C <sub>0</sub>	C <sub>T</sub>	C <sub>0T</sub>	M <sub>A1</sub>	M <sub>A2</sub>	g	kg/m	
BSCN	6	0 -0.015	60-500	2	0.2	14	10.5	25	16.7	1	2.5	1.2	137	225	0.46	0.76	0.39	3.48	14	0.22
	6K				-	12	8	21	12.4	-	2	1.2	71	86	0.25	0.3	0.17	3	8.9	0.19
	8				0.5	16	10.5	27	15.7	1.5	2.5	1.2	137	225	0.6	0.99	0.39	3.82	16	0.39
	8K				-	15	8.5	25	14.6	-	2.5	1.5	119	133	0.55	0.62	3.3	5.6	15.9	0.39
	10				0.5	21	13	33	20	1.5	3	1.5	285	397	1.62	2.25	0.95	8.53	37	0.6
	10K	-	19	11	30	18.2	-	3	1.8	188	215	1.09	1.25	0.7	1.21	31.5	0.6			
	12K	0 -0.018	60-700	2	-	21	15	35	23	-	3	1.8	218	269	1.48	1.83	1.06	1.83	44	0.87
	13				0.5	24	15	36	23	1.5	3	1.5	396	540	2.89	3.94	1.5	12.46	52	1.03
	15K				-	23	20	40	27	-	3.5	2	418	607	3.13	4.56	2.78	3.32	59.5	1.1
	16				0.5	31	17.5	50	34	2	3.5	2	545	849	4.77	7.43	3.71	26.09	130	1.56
20	1.0				35	29	56	39.7	4	4	2.5	724	1109	7.9	12.09	5.53	38	188	2.44	
20K	-0.021	80-800	-	30	26	50	33	-	4	2.5	660	904	6.6	9.04	4.86	5.8	130	2.02		

## ■ 法兰螺帽型



①代号	类型	D 公差	材质				硬度
			花键轴		花键母		
			国标	相当	国标	相当	
BSFN	法兰螺帽型	h7	GCr15	SUJ2	GCr15	SUJ2	高频淬火 58-62HRC

视角标准：第一视角




①代号 - ②D - ③L  
BSFN - D8 - L200

订购编号示例

①代号	花键轴		滚珠列数	C 倒角	花键母							基本额定负载 (kgf)		基本额定扭矩 (kgf·m)		容许静力矩 (kgf·m)		重量					
	②D <sub>h7</sub>	③L 最小单位1			D <sub>1</sub>	L <sub>2</sub>	D <sub>2</sub>	T	F	Q 油孔	A	X	Y	Z	C	C <sub>0</sub>	C <sub>T</sub>	C <sub>0T</sub>	M <sub>A1</sub>	M <sub>A2</sub>	g	kg/m	
BSFN	6	0 -0.015	60-500	2	0.2	14	25	30	6	7.5	1	22	3.4	6.5	4.5	137	225	0.46	0.76	0.39	3.48	36.7	0.22
						16	27	32	8														
	10	0	60-700	2	0.5	21	33	42	9	10.5	1.5	32	4	8	4	285	397	1.62	2.25	0.95	8.53	100	0.6
						24	36	44	11														
	16	0	70-700	2	1.0	31	5	51	10	18	2	42	5.5	9.5	5.4	724	1109	7.9	12.09	5.53	38	226	1.56
						35	56	58	18														
20	-0.021	80-800	-	1.0	35	56	58	10	18	2	42	5.5	9.5	5.4	724	1109	7.9	12.09	5.53	38	303	2.44	



交货期



5天发货



优惠价

数量	1-9	10~
价格	100%	现询

B1  
滚珠花键  
直筒轴承