


加强型

软管箍

★ 产品特点: 为标准型加强扭力的焊接产品, 大幅提升扭力



①代号 - ②W - ③D
HCSSR - W9 - D12

①代号	②W	使用口径			T	紧固扭矩(N·m)
		③D max	Dmin	Dmax		
HCSSS	9	12	8	1/2	0.6	2.5-3.5
		16	10	5/8		
		20	12	3/4		
		22	12	7/8		
		25	16	1		
		27	16	1-1/16		
		32	20	1-1/4		
		40	25	1-5/8		
		45	30	1-3/4		
		50	32	2		
		60	40	2-3/8		
		12	25	16		
	27		16	1-1/16		
	32		20	1-1/4		
	40		25	1-5/8		
	45		30	1-3/4		
	50		32	2		
	60		40	2-3/8		
	70		50	2-3/4		
	80		60	3-1/8		
	90		70	3-1/2		
	100		80	4		
	110		90	4-3/8		
	120	100	4-3/4			
130	110	5-1/8				
140	120	5-1/2				
150	130	5-7/8				
160	140	6-1/4				
170	150	6-3/4				
180	160	7				
190	170	7-1/2				
200	180	7-7/8				
210	190	8-3/4				
220	200	9-1/2				
230	210	9-1/8				

K1 平键、挡圈、开口销、圆柱销、油嘴