


双列角接触球轴承 带橡胶密封圈型

★ 产品特点: 适用于负载较大的场景



型号
BCH-3200DD

代号	型号	d	D	B	r(min)	基本额定负载		容许转速rpm (参考)	d _s (min)	d _s (max)	r (max)	重量 kg (参考)
						Cr(动)kN	Cor(静)kN					
	3800DD		19	7		2.58	1.56	13000		17		0.015
	3900DD		22	10	0.3	4.08	2.36	12400	12	18	0.3	0.022
	3000DD		26	12		5.5	3.2	13600		24		0.052
	3200DD		30	14.3	0.6	7	3.8	15000	14.5	25.5	0.6	0.112
	3300DD		35	19		9.2	5.1	14200	16	31.5		0.018
	3801DD		21	7		2.89	1.92	12000		19		0.026
	3901DD		24	10	0.3	4.36	2.72	11400	14	12	0.3	0.025
	3001DD		28	12		6.1	3.7	12600		26		0.063
	3201DD		32	15.9	0.6	9.2	5.1	14000	16.5	27.5	0.6	0.123
	3301DD		37	19		10	6.1	13200	18	33.5		0.022
	3802DD		24	7		3.09	2.31	9200		22		0.036
	3902DD		28	10	0.3	4.55	3.12	8800	17	15	0.3	0.072
	3002DD		32	13		8.5	5.4	9600		30		0.132
	3202DD		35	15.9	0.6	10	6.1	12000	19.5	30.5	0.6	0.240
	3302DD		42	19	1	12.8	7.9	10000	20.5	36.5	1	0.027
	3803DD		26	7		3.17	2.52	8600		24		0.042
	3903DD		30	10	0.3	4.99	3.79	8200	19	17	0.3	0.100
	3003DD		35	14		9	6	9000		33		0.020
	3203DD		40	17.5	0.6	12.8	7.9	11000	21.5	35.5	0.6	0.046
	3303DD		47	22.2	1	20.4	12.1	9400	22.5	41.5	1	0.080
	3804DD		32	10	0.3	4.9	3.9	7400	22	30	0.3	0.170
	3904DD		37	13		9.3	6.6	7000	21	23		0.230
	3004DD		42	16	0.6	14.2	9.6	7800	23.2	38.8	0.6	0.025
	3204DD		47	20.6	1	19	12.1	9000	25.5	41.5	1	0.062
	3304DD		52	22.2	1.1	20.6	12.7	8200	27	45	0.3	0.062
	3805DD		37	10	0.3	5.5	4.9	6000		35		0.100
	3905DD		42	13		9.6	7.5	5600	26	28		0.190
	3005DD		47	16	0.6	15.2	11	6400	28.2	43.8	0.6	0.369
	3205DD		52	20.6	1	20.6	14.3	7800	30.5	46.5	1	0.030
	3305DD		62	25.4	1.1	30.5	20.5	6800		55		0.095
	3806DD		42	10	0.3	5.7	5.6	5000	32	40	0.3	0.160
	3906DD		47	13		9.9	8.3	4600	31	33		0.320
	3006DD		55	19	1	20.3	15.5	5400	34.6	50.4	1	0.585
	3206DD		62	23.8		28.6	20.4	6500	35.5	56.5		0.035
	3306DD		72	30.2	1.1	39.5	27.5	5800		65		0.138
	3807DD		47	10	0.3	6.1	6.2	4400	37	45	0.3	0.240
	3907DD		55	15		12.9	11.3	4000	36	38		0.480
	3007DD		62	20	1	24.2	20.4	4800	39.6	57.4	1	0.816
	3207DD		72	27	1.1	38	27.8	5600	42	65		0.040
	3307DD		80	34.9	1.5	49.5	35	5200	43.5	71.5	1.5	0.158
	3808DD		52	10	0.3	6.4	6.9	3800	42	50	0.3	0.279
	3908DD		62	16		17.4	15.8	3400	41	43		0.650
	3008DD		68	21	1	24.5	20.8	4200	44.6	63.4	1	1.070
	3208DD		80	30.2	1.1	42.5	32.5	5000	47	73		0.055
	3308DD		90	36.5	1.5	60.5	44	4600	48.5	81.5	1.5	0.183
	3809DD		58	10	0.3	6.7	7.7	3300	47	56	0.3	0.364
	3909DD		68	16		17.9	17.2	2900	46	49		0.710
	3009DD		75	23	1	39.3	36.4	3700	48	66	1	1.420
	3209DD		85	30.2	1.1	48	37.0	4600	52	78		0.075
	3309DD		100	39.7	1.5	72.5	54	4100	53.5	91.5	1.5	0.189
	3810DD		65	12	0.3	7.0	8.4	3000	52	63	0.3	0.395
	3910DD		72	16		19.1	19.6	2600	51	56		0.760
	3010DD		80	23	1.5	42.3	41.9	3400	53	73	1.5	1.950
	3210DD		90	30.2	1.1	51	42.0	4300	57	83	1	0.010
	3310DD		110	44.4	2	85.5	64.5	3800	60	100	2	0.282
	3811DD		72	13	0.3	12.8	15.4	3000	57	70	0.3	0.581
	3911DD		80	19		20	21.7	2600	56	63		1.050
	3011DD		90	26	1.5	43.7	44.7	3400	58	80	1.5	2.530
	3211DD		100	33.3		63	53.0	3900	63.5	91.5		0.140
	3311DD		120	49.2	2	106	82	3400	65	110	2	0.303
	3812DD		78	14	0.3	13.6	16.2	2300	62	76	0.3	0.621
	3912DD		85	19		21	23.8	1900	61	69		1.400
	3012DD		95	26	1.5	47.2	53.4	2700	63	86	1.5	3.240
	3212DD		110	36.5		71.5	58.5	3500	68.5	101.5		
	3312DD		130	54	2.1	122	95.5	3100	72	118	2	

▲ 1kgf=9.8N ▲ 不承诺此产品品牌 ▲ 更多规格请咨询客服



交货期

4天发货